

Specification Sheet

Part Number: 151-01397

- Connector clip design to meet USCAR EWCAP-005-7 clip slot specifications, assuring compliance.
- Meets installation and extraction requirements of SAE/USCAR-2, delivering easy insertion with reliable performance.
- Long fir tree designed for use in thicker panels up to 9.5 mm.
- Oval fir tree prevents rotation in 9x17 mm holes.



Connector Clip with Oval Fir Tree, 9.0 - 17.0mm Hole Dia, PA66HIRHSUV, Black, 2000/carton

Article Number	151-01397
Type	CC20
Color	Black (BK)
Quantity Per	carton
Product Description	Connector Clips are designed with various fixing point designs, to accommodate the many connectors out in the market. This specific connector clip is designed for a commonly used automotive connector. The width and the height of the fixation point creates minimal rattle when secured. The innovative design of the fir tree creates an interface with four different size holes that are common in the automotive industry. The fir tree branch design on all four sides makes a 360-degree interface with the panel, creating a more secure fit into the hole.

Short Description	Connector Clip with Oval Fir Tree, 9.0 - 17.0mm Hole Dia, PA66HIRHSUV, Black, 2000/carton
Global Part Name	CC20-PA66HIRHSUV-BK
Minimum Tensile Strength (Imperial)	35
Minimum Tensile Strength (Metric)	155
Length L (Imperial)	1.00
Length L (Metric)	25.5
Fixation Method	Fir Tree for oval holes
Variant	9.0 x 17.0 mm
Width W (Imperial)	0.80
Width W (Metric)	20.3
Height H (Imperial)	1.03
Height H (Metric)	26.1
Panel Thickness Min (Imperial)	0.02
Panel Thickness Max (Imperial)	0.37
Panel Thickness Min (Metric)	0.6
Panel Thickness Max (Metric)	9.5

Mounting Hole Diameter D (Imperial)	0.35 x 0.67
Mounting Hole Diameter D (Metric)	9.0 x 17.0 mm
Mounting Hole Diameter D Min (Imperial)	0.35
Mounting Hole Diameter D Max (Imperial)	0.35
Mounting Hole Diameter D Max (Metric)	9.0
Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Material Shortcut	PA66HIRHSUV
Flammability	UL 94 HB
UV Resistant (Yes/No)	Yes
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	2000
Package Quantity (Metric)	2000

About HellermannTyton

HellermannTyton is a global manufacturer of cable management and identification solutions for automotive, solar, electrical, construction, industrial automation, broadband and other OEM markets. The company's integrated approach to product design, sustainability, production, quality assurance and delivery is optimized to benefit local and global customers. HellermannTyton operates in 40 countries, with North American headquarters in Milwaukee, Wisconsin. (www.hellermann.tyton.com).

© 2024 HellermannTyton. All Rights Reserved.

[Contact Us](#)

[RoHS/WEEE Compliance](#)

[Disclaimer](#)

[Terms and Conditions](#)