

# N-Channel Logic Level Enhancement Mode Field Effect Transistor



## BSS123

### General Description

These N-Channel enhancement mode field effect transistors are produced using onsemi's proprietary, high cell density, DMOS technology. These products have been designed to minimize on-state resistance while provide rugged, reliable, and fast switching performance. These products are particularly suited for low voltage, low current applications such as small servo motor control, power MOSFET gate drivers, and other switching applications.


### Features

- 0.17 A, 100 V
  - $R_{DS(on)} = 6 \Omega @ V_{GS} = 10 V$
  - $R_{DS(on)} = 10 \Omega @ V_{GS} = 4.5 V$
- High Density Cell Design for Extremely Low  $R_{DS(on)}$
- Rugged and Reliable
- Compact Industry Standard SOT-23 Surface Mount Package
- This Device is Pb-Free and Halogen Free



SOT-23  
CASE 318  
STYLE 21

### MARKING DIAGRAM



SA = Specific Device Code  
M = Date Code\*  
▪ = Pb-Free Package

(Note: Microdot may be in either location)

\*Date Code orientation and/or position may vary depending upon manufacturing location.

### ORDERING INFORMATION

| Device | Package          | Shipping <sup>†</sup> |
|--------|------------------|-----------------------|
| BSS123 | SOT-23 (Pb-Free) | 3000 / Tape & Reel    |

<sup>†</sup> For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specification Brochure, [BRD8011/D](#).

### DISCONTINUED (Note 1)

| Device   | Package          | Shipping           |
|----------|------------------|--------------------|
| BSS123-G | SOT-23 (Pb-Free) | 3000 / Tape & Reel |

- DISCONTINUED:** These devices are not recommended for new design. Please contact your onsemi representative for information. The most current information on these devices may be available on [www.onsemi.com](#).

**ABSOLUTE MAXIMUM RATINGS**  $T_A = 25\text{ }^{\circ}\text{C}$  unless otherwise noted.

| Symbol         | Parameter                                                                 | Ratings         | Unit                   |
|----------------|---------------------------------------------------------------------------|-----------------|------------------------|
| $V_{DS}$       | Drain-Source Voltage                                                      | 100             | V                      |
| $V_{GS}$       | Gate-Source Voltage                                                       | $\pm 20$        |                        |
| $I_D$          | Drain Current – Continuous (Note 2)                                       | 0.17            | A                      |
|                | Drain Current – Pulsed (Note 2)                                           | 0.68            |                        |
| $P_D$          | Maximum Power Dissipation (Note 2)                                        | 0.36            | W                      |
|                | Derate Above $25\text{ }^{\circ}\text{C}$                                 | 2.8             | mW/ $^{\circ}\text{C}$ |
| $T_J, T_{STG}$ | Operating and Storage Junction Temperature Range                          | $-55$ to $+150$ | $^{\circ}\text{C}$     |
| $T_L$          | Maximum Lead Temperature for Soldering Purposes, 1/16" from Case for 10 s | 300             |                        |

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

**THERMAL CHARACTERISTICS**  $T_A = 25\text{ }^{\circ}\text{C}$  unless otherwise noted.

| Symbol          | Parameter                                        | Ratings | Unit                        |
|-----------------|--------------------------------------------------|---------|-----------------------------|
| $R_{\theta JA}$ | Thermal Resistance, Junction-to-Ambient (Note 2) | 350     | $^{\circ}\text{C}/\text{W}$ |

**ELECTRICAL CHARACTERISTICS**  $T_A = 25\text{ }^{\circ}\text{C}$  unless otherwise noted.

| Symbol | Parameter | Test Conditions | Min | Typ | Max | Unit |
|--------|-----------|-----------------|-----|-----|-----|------|
|--------|-----------|-----------------|-----|-----|-----|------|

**OFF CHARACTERISTICS**

|                                     |                                           |                                                                                 |     |    |          |                        |
|-------------------------------------|-------------------------------------------|---------------------------------------------------------------------------------|-----|----|----------|------------------------|
| $BV_{DS}$                           | Drain-Source Breakdown Voltage            | $V_{GS} = 0\text{ V}, I_D = 250\text{ }\mu\text{A}$                             | 100 | –  | –        | V                      |
| $\frac{\Delta BV_{DS}}{\Delta T_J}$ | Breakdown Voltage Temperature Coefficient | $I_D = 250\text{ }\mu\text{A}$ , Referenced to $25\text{ }^{\circ}\text{C}$     | –   | 97 | –        | mV/ $^{\circ}\text{C}$ |
| $I_{DSS}$                           | Zero Gate Voltage Drain Current           | $V_{DS} = 100\text{ V}, V_{GS} = 0\text{ V}$                                    | –   | –  | 1        | $\mu\text{A}$          |
|                                     |                                           | $V_{DS} = 100\text{ V}, V_{GS} = 0\text{ V}, T_J = 125\text{ }^{\circ}\text{C}$ | –   | –  | 60       |                        |
|                                     |                                           | $V_{DS} = 20\text{ V}, V_{GS} = 0\text{ V}$                                     | –   | –  | 10       | nA                     |
| $I_{GSS}$                           | Gate-Body Leakage                         | $V_{GS} = \pm 20\text{ V}, V_{DS} = 0\text{ V}$                                 | –   | –  | $\pm 50$ | nA                     |

**ON CHARACTERISTICS** (Note 3)

|                                        |                                                |                                                                                |      |        |    |                        |
|----------------------------------------|------------------------------------------------|--------------------------------------------------------------------------------|------|--------|----|------------------------|
| $V_{GS(th)}$                           | Gate Threshold Voltage                         | $V_{DS} = V_{GS}, I_D = 1\text{ mA}$                                           | 0.8  | 1.7    | 2  | V                      |
| $\frac{\Delta V_{GS(th)}}{\Delta T_J}$ | Gate Threshold Voltage Temperature Coefficient | $I_D = 1\text{ mA}$ , Referenced to $25\text{ }^{\circ}\text{C}$               | –    | $-2.7$ | –  | mV/ $^{\circ}\text{C}$ |
| $R_{DS(on)}$                           | Static Drain-Source On-Resistance              | $V_{GS} = 10\text{ V}, I_D = 0.17\text{ A}$                                    | –    | 1.2    | 6  | $\Omega$               |
|                                        |                                                | $V_{GS} = 4.5\text{ V}, I_D = 0.17\text{ A}$                                   | –    | 1.3    | 10 |                        |
|                                        |                                                | $V_{GS} = 10\text{ V}, I_D = 0.17\text{ A}, T_J = 125\text{ }^{\circ}\text{C}$ | –    | 2.2    | 12 |                        |
| $I_{D(on)}$                            | On-State Drain Current                         | $V_{GS} = 10\text{ V}, V_{DS} = 5\text{ V}$                                    | 0.68 | –      | –  | A                      |
| $g_{FS}$                               | Forward Transconductance                       | $V_{DS} = 10\text{ V}, I_D = 0.17\text{ A}$                                    | 0.08 | 0.8    | –  | S                      |

**DYNAMIC CHARACTERISTICS**

|           |                              |                                                                 |   |     |   |          |
|-----------|------------------------------|-----------------------------------------------------------------|---|-----|---|----------|
| $C_{iss}$ | Input Capacitance            | $V_{DS} = 25\text{ V}, V_{GS} = 0\text{ V}, f = 1.0\text{ MHz}$ | – | 73  | – | pF       |
| $C_{oss}$ | Output Capacitance           |                                                                 | – | 7   | – |          |
| $C_{rss}$ | Reverse Transfer Capacitance |                                                                 | – | 3.4 | – |          |
| $R_G$     | Gate Resistance              | $V_{GS} = 15\text{ mV}, f = 1.0\text{ MHz}$                     | – | 2.2 | – | $\Omega$ |

**ELECTRICAL CHARACTERISTICS**  $T_A = 25\text{ }^{\circ}\text{C}$  unless otherwise noted. (continued)

| Symbol                                    | Parameter           | Test Conditions                                                                                          | Min | Typ | Max | Unit |
|-------------------------------------------|---------------------|----------------------------------------------------------------------------------------------------------|-----|-----|-----|------|
| <b>SWITCHING CHARACTERISTICS</b> (Note 3) |                     |                                                                                                          |     |     |     |      |
| $t_{d(on)}$                               | Turn-On Delay Time  | $V_{DD} = 30\text{ V}$ , $I_D = 0.28\text{ A}$ ,<br>$V_{GS} = 10\text{ V}$ , $R_{GEN} = 6\text{ }\Omega$ | –   | 1.7 | 3.4 | ns   |
| $t_r$                                     | Turn-On Rise Time   |                                                                                                          | –   | 9   | 18  |      |
| $t_{d(off)}$                              | Turn-Off Delay Time |                                                                                                          | –   | 17  | 31  |      |
| $t_f$                                     | Turn-Off Fall Time  |                                                                                                          | –   | 2.4 | 5   |      |
| $Q_g$                                     | Total Gate Charge   | $V_{DS} = 30\text{ V}$ , $I_D = 0.22\text{ A}$ ,<br>$V_{GS} = 10\text{ V}$                               | –   | 1.8 | 2.5 | nC   |
| $Q_{gs}$                                  | Gate-Source Charge  |                                                                                                          | –   | 0.2 | –   |      |
| $Q_{gd}$                                  | Gate-Drain Charge   |                                                                                                          | –   | 0.3 | –   |      |

**DRAIN-SOURCE DIODE CHARACTERISTICS AND MAXIMUM RATINGS**

|                 |                                                       |                                                                     |   |     |      |    |
|-----------------|-------------------------------------------------------|---------------------------------------------------------------------|---|-----|------|----|
| I <sub>S</sub>  | Maximum Continuous Drain-Source Diode Forward Current |                                                                     | – | –   | 0.17 | A  |
| V <sub>SD</sub> | Drain-Source Diode Forward Voltage                    | V <sub>GS</sub> = 0 V, I <sub>S</sub> = 0.44 A (Note 3)             | – | 0.8 | 1.3  | V  |
| t <sub>rr</sub> | Diode Reverse Recovery Time                           | I <sub>F</sub> = 0.17 A, d <sub>i</sub> f/d <sub>t</sub> = 100 A/μs | – | 11  | –    | ns |
| Q <sub>rr</sub> | Diode Reverse Recovery Charge                         |                                                                     | – | 3   | –    | nC |

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.

2.  $R_{\theta JA}$  is the sum of the junction-to-case and case-to-ambient thermal resistance where the case thermal reference is defined as the solder mounting surface of the drain pins.  $R_{\theta JA}$  is guaranteed by design while  $R_{\theta JA}$  is determined by the user's board design.

a)  $350\text{ }^{\circ}\text{C}/\text{W}$  when mounted on a minimum pad.



3. Pulse Test: Pulse Width  $\leq 300\text{ }\mu\text{s}$ , Duty Cycle  $\leq 2.0\%$


**TYPICAL CHARACTERISTICS**

Figure 1. On-Region Characteristics




Figure 2. On-Resistance Variation with Drain Current and Gate Voltage

## TYPICAL CHARACTERISTICS (continued)




Figure 3. On-Resistance Variation with Temperature




Figure 4. On-Resistance Variation with Gate-to-Source Voltage




Figure 5. Transfer Characteristics




Figure 6. Body Diode Forward Voltage Variation with Source Current and Temperature




Figure 7. Gate Charge Characteristics




Figure 8. Capacitance Characteristics

TYPICAL CHARACTERISTICS (continued)




Figure 9. Maximum Safe Operating Area




Figure 10. Single Pulse Maximum Power Dissipation




Figure 11. Transient Thermal Response Curve


Thermal characterization performed using the conditions described in Note 2a.  
Transient thermal response will change depending on the circuit board design.

## REVISION HISTORY

| Revision | Description of Changes                       | Date       |
|----------|----------------------------------------------|------------|
| 12       | Case outline diagram corrected to style #21. | 10/31/2025 |

This document has undergone updates prior to the inclusion of this revision history table. The changes tracked here only reflect updates made on the noted approval dates.









SCALE 4:1

SOT-23 (TO-236) 2.90x1.30x1.00 1.90P  
CASE 318  
ISSUE AU

DATE 14 AUG 2024




| MILLIMETERS |      |      |      |
|-------------|------|------|------|
| DIM         | MIN  | NOM  | MAX  |
| A           | 0.89 | 1.00 | 1.11 |
| A1          | 0.01 | 0.06 | 0.10 |
| b           | 0.37 | 0.44 | 0.50 |
| c           | 0.08 | 0.14 | 0.20 |
| D           | 2.80 | 2.90 | 3.04 |
| E           | 1.20 | 1.30 | 1.40 |
| e           | 1.78 | 1.90 | 2.04 |
| L           | 0.30 | 0.43 | 0.55 |
| L1          | 0.35 | 0.54 | 0.69 |
| HE          | 2.10 | 2.40 | 2.64 |
| T           | 0°   | ---  | 10°  |

NOTES:


1. DIMENSIONING AND TOLERANCING PER ASME Y14.5M, 2018.
2. CONTROLLING DIMENSIONS: MILLIMETERS.
3. MAXIMUM LEAD THICKNESS INCLUDES LEAD FINISH. MINIMUM LEAD THICKNESS IS THE MINIMUM THICKNESS OF THE BASE MATERIAL.
4. DIMENSIONS D AND E DO NOT INCLUDE MOLD FLASH, PROTRUSIONS, OR GATE BURRS.

GENERIC  
MARKING DIAGRAM\*



XXX = Specific Device Code  
M = Date Code  
▪ = Pb-Free Package

\*This information is generic. Please refer to device data sheet for actual part marking. Pb-Free indicator, "G" or microdot "▪", may or may not be present. Some products may not follow the Generic Marking.



\* For additional information on our Pb-Free strategy and soldering details, please download the onsemi Soldering and Mounting Techniques Reference Manual, SOLDERM/D.

STYLES ON PAGE 2

|                  |                                      |                                                                                                                                                                                     |
|------------------|--------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| DOCUMENT NUMBER: | 98ASB42226B                          | Electronic versions are uncontrolled except when accessed directly from the Document Repository.<br>Printed versions are uncontrolled except when stamped "CONTROLLED COPY" in red. |
| DESCRIPTION:     | SOT-23 (TO-236) 2.90x1.30x1.00 1.90P | PAGE 1 OF 2                                                                                                                                                                         |

onsemi and onsemi are trademarks of Semiconductor Components Industries, LLC dba onsemi or its subsidiaries in the United States and/or other countries. onsemi reserves the right to make changes without further notice to any products herein. onsemi makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. onsemi does not convey any license under its patent rights nor the rights of others.

**SOT-23 (TO-236) 2.90x1.30x1.00 1.90P**  
**CASE 318**  
**ISSUE AU**

DATE 14 AUG 2024

|                                                         |                                                       |                                                             |                                                             |                                                             |                                                             |
|---------------------------------------------------------|-------------------------------------------------------|-------------------------------------------------------------|-------------------------------------------------------------|-------------------------------------------------------------|-------------------------------------------------------------|
| STYLE 1 THRU 5:<br>CANCELLED                            | STYLE 6:<br>PIN 1. BASE<br>2. EMITTER<br>3. COLLECTOR | STYLE 7:<br>PIN 1. EMITTER<br>2. BASE<br>3. COLLECTOR       | STYLE 8:<br>PIN 1. ANODE<br>2. NO CONNECTION<br>3. CATHODE  |                                                             |                                                             |
| STYLE 9:<br>PIN 1. ANODE<br>2. ANODE<br>3. CATHODE      | STYLE 10:<br>PIN 1. DRAIN<br>2. SOURCE<br>3. GATE     | STYLE 11:<br>PIN 1. ANODE<br>2. CATHODE<br>3. CATHODE-ANODE | STYLE 12:<br>PIN 1. CATHODE<br>2. CATHODE<br>3. ANODE       | STYLE 13:<br>PIN 1. SOURCE<br>2. DRAIN<br>3. GATE           | STYLE 14:<br>PIN 1. CATHODE<br>2. GATE<br>3. ANODE          |
| STYLE 15:<br>PIN 1. GATE<br>2. CATHODE<br>3. ANODE      | STYLE 16:<br>PIN 1. ANODE<br>2. CATHODE<br>3. CATHODE | STYLE 17:<br>PIN 1. NO CONNECTION<br>2. ANODE<br>3. CATHODE | STYLE 18:<br>PIN 1. NO CONNECTION<br>2. CATHODE<br>3. ANODE | STYLE 19:<br>PIN 1. CATHODE<br>2. ANODE<br>3. CATHODE-ANODE | STYLE 20:<br>PIN 1. CATHODE<br>2. ANODE<br>3. GATE          |
| STYLE 21:<br>PIN 1. GATE<br>2. SOURCE<br>3. DRAIN       | STYLE 22:<br>PIN 1. RETURN<br>2. OUTPUT<br>3. INPUT   | STYLE 23:<br>PIN 1. ANODE<br>2. ANODE<br>3. CATHODE         | STYLE 24:<br>PIN 1. GATE<br>2. DRAIN<br>3. SOURCE           | STYLE 25:<br>PIN 1. ANODE<br>2. CATHODE<br>3. GATE          | STYLE 26:<br>PIN 1. CATHODE<br>2. ANODE<br>3. NO CONNECTION |
| STYLE 27:<br>PIN 1. CATHODE<br>2. CATHODE<br>3. CATHODE | STYLE 28:<br>PIN 1. ANODE<br>2. ANODE<br>3. ANODE     |                                                             |                                                             |                                                             |                                                             |

|                  |                                      |                                                                                                                                                                                     |
|------------------|--------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| DOCUMENT NUMBER: | 98ASB42226B                          | Electronic versions are uncontrolled except when accessed directly from the Document Repository.<br>Printed versions are uncontrolled except when stamped "CONTROLLED COPY" in red. |
| DESCRIPTION:     | SOT-23 (TO-236) 2.90x1.30x1.00 1.90P | PAGE 2 OF 2                                                                                                                                                                         |

**onsemi** and **onsemi** are trademarks of Semiconductor Components Industries, LLC dba **onsemi** or its subsidiaries in the United States and/or other countries. **onsemi** reserves the right to make changes without further notice to any products herein. **onsemi** makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does **onsemi** assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. **onsemi** does not convey any license under its patent rights nor the rights of others.

**onsemi**, **Onsemi**, and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "**onsemi**" or its affiliates and/or subsidiaries in the United States and/or other countries. **onsemi** owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of **onsemi**'s product/patent coverage may be accessed at [www.onsemi.com/site/pdf/Patent-Marking.pdf](http://www.onsemi.com/site/pdf/Patent-Marking.pdf). **onsemi** reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and **onsemi** makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does **onsemi** assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using **onsemi** products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by **onsemi**. "Typical" parameters which may be provided in **onsemi** data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. **onsemi** does not convey any license under any of its intellectual property rights nor the rights of others. **onsemi** products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use **onsemi** products for any such unintended or unauthorized application, Buyer shall indemnify and hold **onsemi** and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that **onsemi** was negligent regarding the design or manufacture of the part. **onsemi** is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

## ADDITIONAL INFORMATION

### TECHNICAL PUBLICATIONS:

Technical Library: [www.onsemi.com/design/resources/technical-documentation](http://www.onsemi.com/design/resources/technical-documentation)  
onsemi Website: [www.onsemi.com](http://www.onsemi.com)

### ONLINE SUPPORT: [www.onsemi.com/support](http://www.onsemi.com/support)

For additional information, please contact your local Sales Representative at  
[www.onsemi.com/support/sales](http://www.onsemi.com/support/sales)

