

COAXIAL CONNECTOR, TNC, 50 Ohm, Straight cable plug (male)
11_TNC-50-6-8/12-_N

Properties

- Suitable for use with Eacon_6C cable
- Applicable in frequencies up to 11 GHz
- Compliant with MIL-STD-348A/313 interface standard



Product configuration		
Interface type	Gender	Standard
TNC	plug	IEC 60169-17_MIL-STD-348A/313_CECC 22200

Interface and material data		
Piece parts	Material	Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer conductor	Brass	Nickel Plating
Body	Brass	Nickel Plating
Other body part	Stainless Steel	
Insulator	PTFE (Polytetrafluoroethylene)	
Coupling nut	Stainless Steel	
Gasket	VMQ (Silicone rubber)	

Electrical data	
Impedance	50 Ω
Interface frequency	11 GHz

Electrical Data (frequency related)		
Frequency range	Return loss	VSWR
0 GHz ... 11 GHz	20.8 dB	1.2

Mechanical data	
Mating cycles	500
Cable entry centre contact	plugged
Cable entry outer contact	clamped

COAXIAL CONNECTOR, TNC, 50 Ohm, Straight cable plug (male)
11_TNC-50-6-8/12-_N

Environmental data	
Operation temperature	-60 °C ... 165 °C
Ingress protection (IP Rating)	Mated / IP67

Ordering Information Table		
Item number	Item description	Packaging type
85074232	11_TNC-50-6-8/12-_NE	Single

Suitable cables	
Cable group	U96 - EACON_6C
Suitable cables	EACON_6C

Additional Information	
Only as assembly	No

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/ EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P3382 / Date of publication: 17.07.2024 / uncontrolled copy