

1052600 -1 Product Details

Live Product Chat US Only
8:30am - 5pm ET, Mon - Fri



1052600 -1

[Active](#)

SMA/QMA RF Connectors

[Always EU RoHS/ELV Compliant](#) ([Statement of Compliance](#))

Product Highlights:

- ? Connector
- ? Jack
- ? Connector Type = SMA
- ? Without Snap -Lock
- ? Terminate To Printed Circuit Board

[View all Features](#) | [Find Similar Products](#)

Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)

Documentation & Additional Information

Product Drawings:

- ? [OSM HERMETICALLY SEALED STRAIGHT PANEL JACK RECEPTACLE](#) (PDF, English)

Catalog Pages/Data Sheets:

- ? None Available

Product Specifications:

- ? None Available

Application Specifications:

- ? None Available

Instruction Sheets:

- ? None Available

CAD Files:

- ? None Available

Additional Information:

- ? [Product Line Information](#)

Related Products:

- ? [Tooling](#)

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- ? [Product Type](#) = Connector
- ? [Gender](#) = Jack
- ? [Connector Type](#) = SMA
- ? [Body Style](#) = Straight
- ? [Number of Panel Mount Holes](#) = 4
- ? [PCB Mount Angle](#) = Vertical
- ? [Body Material](#) = Stainless Steel
- ? [Body Finish](#) = Passivated
- ? [Center Contact](#) = With
- ? [Retractable Collar](#) = Without
- ? [Safety Wire Holes](#) = Without
- ? Dielectric Material = PTFE Fluorocarbon
- ? Comment = Hermetically Sealed; Captured Center Contact

Mechanical Attachment:

- ? [Panel Attachment](#) = With
- ? [Panel Attachment Method](#) = Flange
- ? [Panel Attachment Style](#) = Front Mount

Electrical Characteristics:

- ? Impedance (?) = 50

Body Related Features:

- ? Snap -Lock = Without
- ? [Length \(mm \[in\]\)](#) = 12.45 [0.490]
- ? O-Ring Material = Nitrile (Buna -N)

Contact Related Features:

- ? Center Contact Material = Beryllium Copper
- ? Center Contact Plating = Gold

Industry Standards:

- ? Government/Industry Qualification = No
- ? [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- ? [Lead Free Solder Processes](#) = Wave solder capable to 240°C, Wave solder capable to 260°C, Wave solder capable to 265°C
- ? RoHS/ELV Compliance History = Always was RoHS compliant

Conditions for Usage:

- ? [Terminate To](#) = Printed Circuit Board

Other:

- ? Brand = AMP