




Recommended Panel Cut-Out







②Notes:
- QC Important Dimension To Check
- Waterproof Rate: IP67
- LED Holder: Brass, Nickel Plating
- LED: ø3 mm, Green
- O-Ring: EPDM, Black
- Screw Nut: Brass, Nickel Plating
- Operating Voltage: DC 4V
- Operating Temperature: -40~+80°C
- For Panel Thickness 6.5mm Max.
- Forward Voltage: Green Typ. 3.5V/Max.4(V)
- Forward Current: Green Max. 30mA
- Reverse Voltage: DC 5V
- Luminous Intensity: Green Min.2950/Typ.5000(Mcd)

①Nut Torque:2.5~3.5kgf.cm







RoHS compliant

Scale	Free
TOLERANCE	
.X	±0.25
.XX	±0.10
.XXX	±0.05
Angle	±1°

Id.	Modification	Date	Name
②	Update the notes	06.08.2021	Segal
①	Add the nut torque	07.05.2014	Winnie
⓪	Drawn	11.03.2014	Winnie

	Date	Name
Drawn	11.03.2014	Winnie
Approved	06.08.2021	Winnie

ASSMANN WSW components

Customer-No.

ASSMANN WSW-No.
A-LED8-1GAAS-MR7-1

Drawing-No.
ASS 6228 CO

rev02

Replace

Sheet

Downloaded from Arrow.com.