


CONTACT ARRANGEMENT

code for x	function	connected terminals
N	ON - ON	1-2, 4-5 alternating with 2-3, 5-6
R	ON - MOM	rest position: 1-2, 4-5; pushed down: 2-3, 5-6

Specifications:

Contact rating:	3A, 250V AC / 6A, 125V AC 4A, 30V DC / 5A, 12V DC 6A, 6V DC
Contact resistance:	20mOhm max.
Insulation resistance:	1 000MOhm min. at 500V DC
Dielectric strength:	1 500V, 50Hz for the duration of 1 minute
Operating temperature:	-45°C to +140°C
Mechanical life:	min. 30 000 cycles
Operating force:	15 +/-6 N (MPG 206 R)
Soldering conditions:	hand-soldering: max.: 420°C, 3sec., 60W auto-soldering: max.: 270°C, 5sec.
Mounting instruction:	max. torque: 137Ncm
Material:	Terminal / contact: brass, silver plated Case: DAP Housing: stainless steel, CNS9265 Bushing: copper alloy, C3604BD nickel plated Actuator: copper alloy, C3604BD chrome plated
Included accessories:	2 pcs. nut 15/32-32, nickel plated, 14mm wrench size 1 pc. tooth washer 1 pc. locking washer

Compliance: RohS III (2015/863/EU)

Tolerances: 0.00: ±0.25mm 0.0: ±0.40mm		Date	Name	MPG 206 x	
		06/09	dr		
Operating force	10/21	dr		30 18 50	
Contact arrangement	07/15	dr			
Dimension	01/11	dr			
Actuator length	07/09	ok			
Modifications	Date	Name			

knitter-switch

Page

1/1