




OPTIONAL HOUSING

WEBBED KEYING FEATURES

20 CKT HEADER
SHOWN FOR REFERENCE



SECTION B-B

DIMENSIONS SHOWN (METRIC) INCH

UNLESS OTHERWISE SPECIFIED
TOLERANCES: ANGULAR ± 1/2°

	INCH	METRIC
3 PLACE	± .005	
2 PLACE	± .01	± 0.13
1 PLACE		± 0.25

DRAFT WHERE APPLICABLE MUST
REMAIN WITHIN DIMENSIONS

DRWG. BY RKA CHK'D. BY BB
APP'D. BY SM SCALE :

REVISION ONLY ON CAD SYSTEM

TITLE SALES ASSY, SL VERTICAL
HEADER W/LATCH & TRI-PEGS
(2.54)/.100 CENTERS

MOLEX INCORPORATED SHEET NO. 2 DATE 04/7/19
LITSE, ILL. 60532 U.S.A.

PART NO. SD-70545-001
SEE CHART
THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INC. AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

	13	12	11	10	9	8	7	6	5	4	3	2	1												
J	CIRCUIT SIZE	ASSEMBLY ITEM NUMBER 70545	MANUFACTURE RELEASE STATUS				D (± 0.38) ± .015	E (± 0.25) ± .010			CONNECTOR END PLATING			P.C. BOARD END PLATING											
							TYPE	H MEAS.				TYPE	K MEAS.												
I	2-10	-9036 TO -9044	R.F.M.				(3.30) .130	(6.10) .240			15 GOLD	(2.54) .100		TIN	(1.27) .050										
	11-13	-9045 TO -9047	R.F.M.																						
	14	-9048	R.F.M.				(3.30) .130	(6.10) .240			15 GOLD	(2.54) .100		TIN	(1.27) .050										
H	3-4	-9072 to -9073	R.F.M.																						
	8	-9077	R.F.M.				(3.30) .130	(6.10) .240			30 GOLD	(2.54) .100		TIN	(1.27) .050										
	10	-9079	R.F.M.																						
G	12-13	-9081 to -9082	R.F.M.				(3.30) .130	(6.10) .240			30 GOLD	(2.54) .100		TIN	(1.27) .050										
	18	-9087	R.F.M.																						
F																									
E	CIRCUIT SIZE	ASSEMBLY ITEM NUMBER	ASSEMBLY ITEM NUMBER	ASSEMBLY ITEM NUMBER	ASSEMBLY ITEM NUMBER	ASSEMBLY ITEM NUMBER																			
	2		70545-9036																						
D	3		70545-9037		70545-9072																				
	4		70545-9038		70545-9073																				
	5		70545-9039																						
C	6		70545-9040																						
	7		70545-9041																						
	8		70545-9042		70545-9077																				
B	9		70545-9043																						
	10		70545-9044		70545-9079																				
	11		70545-9045																						
A	12		70545-9046		70545-9081																				
	13		70545-9047		70545-9082																				
	14		70545-9048																						
	15		70545-9049																						
	16		70545-9050																						
	17																								
	18		70545-9052		70545-9087																				
	19																								
	20		70545-9054																						
	21																								
	22																								
	23																								
	24																								
	25																								
A							ADD 70545-90** EC NO: UCP2006-0364 2005/12/12 DRAWN BY: CHKD:BBARKER APPR:SMILLER 2005/12/19 REV DESCRIPTION	QUALITY SYMBOLS ▽=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM/IN		SCALE ---	DESIGN UNITS INCH	THIRD ANGLE PROJECTION		B								
	mm		INCH		DRAWN BY RKADAMS	DATE 07/19/2004			TITLE SALES ASSY, SL VERTICAL HEADER W/LATCH&TRI-PEGS (2.54)/.100 CENTERS																
	4 PLACES ± --- ± ---		3 PLACES ± --- ± ---		2 PLACES ± --- ± ---		1 PLACE ± --- ± ---		ANGULAR ± --- °		CHECKED BY BBARKER	DATE 07/19/2004	APPROVED BY SMILLER		DATE 07/19/2004	molex MOLEX INCORPORATED		A							
	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS						MATERIAL NO. SEE TABLE		DOCUMENT NO. SD-70545-001		SHEET NO. 3 OF 4														
THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																									
ib_frame_C_P_ME_T Rev. D 2004/04/02														12	11	10	9	8	7	6	5	4	3	2	1

	13	12	11	10	9	8	7	6	5	4	3	2	1											
J	CIRCUIT SIZE	ASSEMBLY ITEM NUMBER 70545	MANUFACTURE RELEASE STATUS				D REF.	E ± .010		CONNECTOR END PLATING			P.C. BOARD END PLATING											
										TYPE	H MEAS.		TYPE	K MEAS.										
	2-19	-3901-3918	NOT TOOLED	WEBBED ASSEMBLY			(3.30) .130	(6.10) .240		30 GOLD	(2.54) .100		TIN	(1.27) .050										
	20-25	-3919-3924	R.F.M.																					
I	2-19		NOT TOOLED	WEBBED ASSEMBLY			(3.30) .130	(6.10) .240		15 GOLD	(2.54) .100		TIN	(1.27) .050										
	20-25		R.F.M.																					
H	2-19		NOT TOOLED	WEBBED ASSEMBLY			(3.30) .130	(6.10) .240		TIN	(2.54) .100		TIN	(1.27) .050										
	20-25		R.F.M.																					
G																								
F																								
	CIRCUIT SIZE	WEBBED ASSEMBLY ITEM NUMBER	WEBBED ASSEMBLY ITEM NUMBER	WEBBED ASSEMBLY ITEM NUMBER																				
	2																							
	3																							
	4																							
E	5																							
	6																							
	7																							
	8																							
	9																							
D	10																							
	11																							
	12																							
	13																							
C	14																							
	15																							
	16																							
	17																							
	18																							
	19																							
	20																							
	21	70545-3921																						
	22																							
	23	70545-3923																						
	24																							
B	25																							
A							ADD -3921-3923 EC NO: UCP2006-0364 DRWN:BSWART 2005/12/12 CHKD:BBARKER 2005/12/19 APPR:SMILLER 2005/12/19	QUALITY SYMBOLS ▽=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED) mm INCH 4 PLACES ± --- ± --- 3 PLACES ± --- ±.005 2 PLACES ± 0.13 ±.01 1 PLACE ± 0.25 ± --- ANGULAR ±1/2°	DIMENSION STYLE MM/IN DRAWN BY DATE RKA 2004/17/19 CHECKED BY DATE BB 2004/17/19 APPROVED BY DATE SM 2004/17/19	SCALE --- DESIGN UNITS INCH	THIRD ANGLE PROJECTION	SALES ASSY, SL VERTICAL HEADER W/LATCH & TRIPEGS (2.54)/.100 CENTERS	MOLEX INCORPORATED	SHEET NO. 4 OF 4									
																DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS	SEE TABLE	DOCUMENT NO. SD-70545-001						
tb_frame_C_P_ME_T Rev. D 2004/04/02													12	11	10	9	8	7	6	5	4	3	2	1