






# MLK1005SR24JT000

Applications		Commercial Grade
Feature		Multilayer
		No Directivity
		Non-Magnetic Core (Dielectric Ceramic)
Series	MLK Series / MLK1005 Type	
Status	PROD	




Size	
Length(L)	1.00mm +/-0.10mm
Width(W)	0.50mm +/-0.10mm
Thickness(T)	0.50mm +/-0.10mm
Recommended Land Pattern (A)	0.50mm Nom.
Recommended Land Pattern (B)	0.40mm Nom.
Recommended Land Pattern (C)	0.50mm Nom.

Electrical Characteristics	
Inductance	240nH +/-5% at 100MHz
Rated Current (Temperature Rise) [Max.]	70mA (20degC Rise)
Self-Resonant Frequency [Min.]	1GHz
Self-Resonant Frequency [Typ.]	1.3GHz
Q [Min.]	6 at 100MHz
Q [Typ.]	8 at 100MHz
DC Resistance [Nom.]	4.84Ω
DC Resistance [Max.]	6.5Ω


Other	
Operating Temp. Range (Including Self-Temp. Rise)	-55 to 125degC
Soldering Method	Reflow, Iron Soldering
AEC Q200	No
Packing	Punched (Paper)Taping [180mm Reel]
Package Quantity	10000Pcs Min.
Weight	0.001g

# MLK1005SR24JT000


## Characteristic Graphs (This is reference data, and does not guarantee the product's characteristics.)




MLK1005SR24JT000



MLK1005SR24JT000





MLK1005SR24JT000




MLK1005SR24JT000

# MLK1005SR24JT000

## Characteristic Graphs (This is reference data, and does not guarantee the product's characteristics.)



MLK1005SR24JT000(Amb. Temp. = 20degc)



•This PDF document was created based on the data listed on the TDK Corporation website.  
•All specifications are subject to change without notice.