

6

5

4

3


2

1



APPROVED: _____

DATE: _____ TITLE: _____


Rev	AWO #	Description	Date	Appr
-		RELEASED	10/01/08	



SEC. A-A



SEC. B-B



SPECIFICATIONS:

Material:

Contact: Phosphor Bronze, 0.2mm thick

Plating: Tin over copper underplate overall.

Electrical:

Operating voltage: 250 VAC RMS max

Current rating: 20 Awg: 5 Amps max

22 Awg: 5 Amps max

24 Awg: 4 Amps max

26 Awg: 3 Amps max

28 Awg: 2 Amps max

30 Awg: 1 Amp max.

Contact resistance: 10 mohms max.

Dielectric withstanding voltage: 1500 VAC for 1 minute

Temperature rise: 30° max.

Mechanical:

Wire size: 20 Awg thru 30 Awg

Environmental:

Lead free, RoHS compliant.



P/N	Wire size	Dim. a	Dim. b	Dim. c	Dim. d
DMT-A-C-F-T-R	#26~#30AWG	.071 [1.80]	.063 [1.60]	.094 [2.40]	.075 [1.90]
DMT-B-C-F-T-R	#20~#24AWG	.083 [2.10]	.083 [2.10]	.106 [2.70]	.098 [2.50]

UNLESS OTHERWISE SPECIFIED
ALL DIMENSIONS ARE MM [INCHES]
TOLERANCES: EXCEPT AS NOTED

INCHES	HOLES
.X ± .10	Ø.X ± .10
.XX ± .020	Ø.XX ± .015
.XXX ± .015	Ø.XXX ± .010

APPROVALS

DATE

DRAWN

DY

10/01/08

CHECKED

APPROVED

ADAM TECH

909 Rahway Avenue, Union, NJ 07083

Phone: 908-687-5000 Fax: 908-687-5710

TITLE

.118" [3.0mm] CRIMP TERMINAL,
TIN PLATED, ON REEL

SIZE

X

PART NO.

DMT-X-C-F-T-R

REV.

-

REF: S00123T

SCALE: NTS

SHEET 1 OF 1

6

5

4

3

2

1