


## NOTES:

1. MATERIALS AND FINISHES:  
BODY, NUT-HEX & RING - BRASS, NICKEL PLATING  
CONTACT - BeCu, SILVER PLATING  
INSULATOR - PTFE, NATURAL  
GASKET - SILICONE RUBBER, RED
2. ELECTRICAL:  
A. IMPEDANCE: 50 OHM
3. MECHANICAL:  
A. DURABILITY: 500 CYCLES MIN.  
B. TEMPERATURE RANGE: -65° C TO +165° C
4. PACKAGING:  
A. QUANTITY: SINGLE PACK  
B. MARKING: BAG TO BE MARKED  
"AMPHENOL RF, 82-515, AND DATE CODE"



THIRD ANGLE PROJ. 

## REVISONS

REV	DESCRIPTION	DATE	ECO	APPR
--	RELEASE TO MFG.	--	--	
M	REDRAWN IN PRO-E & COD SHEET ADDED	9/3/15	50266	AAP



SCALE 1.000

RECOMMENDED MOUNTING  
HOLE DIMENSIONS
**CUSTOMER OUTLINE DRAWING**  
 ALL OTHER SHEETS ARE FOR INTERNAL USE ONLY

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES AND TOLERANCES ARE: 2 PLACE DECIMAL      3 PLACE DECIMAL      ANGLES ±.015 (0.381 mm)      ±.005 (0.127 mm)      ± 1°	MATERIAL SEE NOTES	DRAWN A ARUN PRABU	DATE 07-Nov-14	TITLE C STR JACK HIGH VOLTAGE RECEPTACLE UG-634/U	Amphenol RF www.amphenolrf.com
NOTICE - These drawings, specifications, or other data (1) are, and remain the property of Amphenol Corp. (2) must be returned upon request; and (3) are confidential and not to be disclosed to any person other than those to whom they are given by Amphenol Corp. the furnishing of these drawings, specifications, or other data by Amphenol Corp., or to any other person to anyone for any purpose is not to be regarded by implication or otherwise in any manner licensing, granting rights to permitting such holder or any other person to manufacture, use or sell any product, process or design, patented or otherwise, that may in any way be related to or disclosed by said drawings, specifications, or other data.	REFERENCE U.S. NAVY REQ-10593	ENGINEER D. ROYCE	DATE 07-Feb-92		DRAWING NO. 82-515
CONFIGURATION LEVEL: In Work	APPROVED K. CAPOZZI	DATE 7/23/15	SCALE: 5.0:1.0	SHEET 2 OF 2	ITEM NO. 82-515
FINISH	CAD FILE		DWG SIZE B	REV M	PART NO. 82-515