

Product data sheet

Specifications



Rack Distribution Panel 208 V

PDRDPF10U-R

⚠ Discontinued on: Aug 29, 2023

⚠ End-of-service on: Feb 21, 2024

⚠ Discontinued

Overview

Lead time Usually Ships within 3 Weeks

Main

Main Input Voltage 208 V 3 phases

Main Output Voltage 120 V
208 V 3 phases

Input Connection Type IEC 60309

Number of rack unit 42U

Number of cables 1

Provided equipment Installation guide
User manual

Physical

Colour Black

Height 206 cm

Width 61 cm

Depth 107.2 cm

Net weight 190 kg

Mounting preference No preference

Mounting mode Not rack-mountable

Input

Network frequency 60 Hz +/- 3 Hz

Max line current 80 A

Load capacity 28800 VA

Conformance

Product certifications cUL listed
UL listed

Environmental

Ambient air temperature for operation 0...40 °C

Relative humidity 0...95 %

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Operating altitude	0...10000 ft
Ambient air temperature for storage	-15...45 °C
Storage Relative Humidity	0...95 %
Storage altitude	0...9144 m

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	226.1 cm
Package 1 Width	91.4 cm
Package 1 Length	121.9 cm
Package 1 Weight	199.581 kg

Contractual warranty

Warranty	1 year repair or replace
----------	--------------------------



Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Use Better

 Materials and Substances	
EU RoHS Directive	Compliant

Use Again

 Repack and remanufacture	
WEEE Label	 The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins