



**Part Number :** [2240881112](#)

**Product Description :** Pre-Crimped Lead Mini-Fit Max Female-to-Pigtail, Matte Tin (Sn) Plating, 150.00mm Length, 14 AWG Wire, Black

**Series Number :** 224088

**Status :** Active

**Product Category :** Power and Signal Cable Assemblies



---

## Documents and Resources


### Drawings

[2240881112 sd.pdf](#)

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)6375-DC (05 Nov 2025) SCIP:343c2ef8-b942-4aba-98fc-7487a48c5eeb
EU RoHS	Compliant per EU 2015/863

### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474

- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

## Part Details

### General

Status	Active
Category	Power and Signal Cable Assemblies
Series	224088
Description	Pre-Crimped Lead Mini-Fit Max Female-to-Pigtail, Matte Tin (Sn) Plating, 150.00mm Length, 14 AWG Wire, Black
Application	Signal, Wire-to-Board
Assembly Configuration	Pre-crimped Lead Only
Connector to Connector	Mini-Fit Max Crimp Terminals
Product Name	Mini-Fit Max
UPC	196823397486

### Electrical

Current - Maximum per Contact	21.0A
Voltage - Maximum	600V AC (RMS)/DC

### Physical

Cable Length	150.00mm
Circuits (Loaded)	1
Circuits (maximum)	1
Color - Resin	Black
Gender	Female-Pigtail
Material - Metal	High Conductivity Copper Alloy
Material - Plating Mating	Matte Tin
Material - Plating Termination	Matte Tin
Net Weight	4.060/g

Number of Rows	1
Packaging Type	Bag
Plating min - Mating	1.020µm
Plating min - Termination	1.020µm
Single Ended	Yes
Termination Interface Style	Crimp or Compression
Wire/Cable Type	UL 11028
Wire Size (AWG)	14

## Mates With / Use With

### Use with Part(s)

Description	Part Number
Mini-Fit Max Dual Row Receptacle Housings	<u>212514</u>
Mini-Fit Max Single Row Receptacle Housings	<u>215913</u>

---

This document was generated on Jan 04, 2026