
© 2017 TE Connectivity Ltd. family of companies. All Rights Reserved







✔ Active

TE CONNECTIVITY (TE)

FASTON .110 REC 0.5 /1.5 MM2 TPBR

FASTON | 110

626041-2
TE Internal Number: 626041-2

EU RoHS Compliant
EU ELV Compliant

Terminal Type Receptacle

Wire Size (AWG) 20 – 15

Wire Size (mm^2) .5 – 1.5

Mating Tab Width 2.8 mm [.11 in]

Mating Tab Thickness .81 mm [.032 in]

PRODUCT DRAWING
English

3D PDF

DOCUMENTATION —

Product Drawings

.110 SERIES FASTON REC.
PDF
English

CAD Files

3D PDF
PDF
3D

Customer View Model

Downloaded from Arrow.com.

2D_DXF.ZIP
English

Customer View Model

3D_IGS.ZIP
English

Customer View Model

3D_STP.ZIP
English

FEATURES

Please review product documents or contact us for the latest agency approval information.

Please Note: Use the Product Drawing for all design activity.

Product Type Features

Terminates To Wire & Cable
FASTON Yes
Insulated Wire Support Yes
Disconnect Type Quick Connect
Insertion Force Normal
Insulated No
Wire/Cable Type Discrete Wire
Wire Stop No
Wire/Cable Composition Stranded

Body Features

Plating Material Tin
Plating Thickness 1 µm [39.37 µin]

Contact Features

Terminal Type Receptacle
Terminal Orientation Straight
Barrel Type Open
Crimp Type F-Crimp

Mechanical Attachment

Mating Retention Type Dimple

Dimensions

Wire Size (AWG) 20 – 15
Wire Size (mm^2) .5 – 1.5
Mating Tab Width 2.8 mm [.11 in]
Mating Tab Thickness .81 mm [.032 in]
Accepts Wire Insulation Diameter Range 2.03 – 3.04 mm [.08 – .119 in]
Receptacle Stock Thickness .25 mm [.01 in]
Wire Insulation Diameter (Max) 3.04 mm [.119 in]
Overall Length 14 mm [.551 in]

Downloaded from Arrow.com.

Usage Conditions

Operating Temperature Range (°C) 100

Industry Standards

UL Rating Listed

Packaging Features

Packaging Method Reel
Packaging Quantity 15000

Other

Line Budget

PRODUCT COMPLIANCE

Statement of Compliance

Statement of Compliance
PDF

Downloaded from Arrow.com.