




PRODUCT NUMBER	PITCH
YK335xx0x0J0G	8.25 mm



MATERIALS & ELECTRICAL
 RATED VOLTAGE & CURRENT: 300 V, 20 A / 300 V, 32 A
 WITHSTAND VOLTAGE: AC 2500V/Min
 INSULATION RESISTANCE: 1000 MΩ OR MORE AT DC 500 V
 OPERATING TEMPERATURE RANG: -40 °C +115 °C
 SCREW TORQUE VALUE: 8.8 Lb-In
 WIRE RANGE: 22 - 12 AWG
 1) HOUSING: Thermoplastic, UL 94 V-0 BLACK
 2) TERMINAL: BRASS, 0.8t
 3) TERMINAL SCREWS: STEEL,M3
 APPROVAL:  

DIMENSION

Dim A	N×8.25+2.0
Dim B	(N-1)×8.25

N=Number of poles

Poles	Tolerance
2p-5p	±0.20
6p-10p	±0.25
11p-16p	±0.35
17p-24p	±0.40
25p-32p	±0.50

PART NO.: YK 335xx 0 x 0 J0G

No. of poles
 02 2 poles
 03 3 poles

 32 32 poles

Plated

Code	Terminal	Screw
0	G/F	G/F
1	G/F	Zinc
2	Tin	G/F
3	Tin	Zinc

RoHS compliant
 (lead<4%)
 In copper Alloy

mat'l. code				surface ASME Y14.5 ✓		tolerance ASME Y14.5		projection 		product family TERMINAL BLOCK																									
ltr		ecn no		dr		date		tolerances unless otherwise specified						title																					
								angles		linear		X.±0.5				TERMINAL BLOCK																			
										X.X±0.3																									
								X'±1"		X.XX±0.1																									
								dr		EVAN LU		061614				dwg no		sheet 1 of 1				size													
								enrg		EVAN LU		061614				YK335xx0x0J0G		A4																	
								chr		HANKE FENG		061614																							
								appd		SHI JUN		061614				type		CUSTOMER Drawing																	
sheet index		revision sheet		A 1																															