**Part Number :** 5023520400
**Product Description :** DuraClik Wire-to-Board Header, Single Row, Right-Angle, 4 Circuits, Tin (Sn) Plating, Natural
**Series Number :** 502352
**Status :** Active
**Product Category :** PCB Headers and Receptacles



## Documents and Resources

### Drawings

5023520400_sd.pdf

### 3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

Symbol and Footprint (Multi-Format)

### Specifications

PK-502352-002-JP-001.pdf

## Product Environment Compliance

### Compliance

| | |
|---|---|
| GADSL/IMDS | Compliant with Exemption 44; 33 |
| China RoHS | per SJ/T 11365-2006 |
| EU ELV | Compliant per 2000/53/EC |
| Low-Halogen Status | Not Low-Halogen per IEC 61249-2-21 |
| REACH SVHC | Not Contained per D(2025)7771-DC (04 Feb 2026) |
| EU RoHS | Compliant per EU 2015/863 |

Compliance Statements

- EU RoHS

Downloaded from Arrow.com.

- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

---

## Part Details

### General

| | |
|---|---|
| Status | Active |
| Category | PCB Headers and Receptacles |
| Series | 502352 |
| Description | DuraClik Wire-to-Board Header, Single Row, Right-Angle, 4 Circuits, Tin (Sn) Plating, Natural |
| Application | Automotive, Signal, Wire-to-Board |
| Comments | The Operating Temperature Range when used with DuraClik series 502351 is -40°C to +105°C. It is -40°C to 125°C when used with DuraClik ISL series 560123 or TPA series 505151. |
| Component Type | PCB Header |
| Product Name | DuraClik |
| UPC | 800756731728 |

### Agency

| | |
|---|---|
| UL | E29179 |

### Electrical

| | |
|---|---|
| Current - Maximum per Contact | 3.0A |
| Voltage - Maximum | 125V |

Downloaded from Arrow.com.

## Physical

| | |
|---|---|
| Breakaway | No |
| Circuits (Loaded) | 4 |
| Circuits (maximum) | 4 |
| Color - Resin | Natural |
| Durability (mating cycles max) | 30 |
| First Mate / Last Break | No |
| Glow-Wire Capable | No |
| Keying to Mating Part | No |
| Lock to Mating Part | Yes |
| Mated Height | 6.40mm |
| Material - Metal | Copper Alloy |
| Material - Plating Mating | Tin |
| Material - Resin | Polyamide (PA) |
| Net Weight | 0.600/g |
| Number of Rows | 1 |
| Orientation | Right Angle |
| Packaging Type | Embossed Tape on Reel |
| PCB Locator | No |
| PCB Retention | Yes |
| Pitch - Mating Interface | 2.00mm |
| Pitch - Termination Interface | 2.00mm |
| Polarized to Mating Part | Yes |
| Polarized to PCB | Yes |
| Stackable | No |
| Temperature Range - Operating | -40° to +105°C, -40° to +125°C |
| Termination Interface Style | Surface Mount |

## Solder Process Data

| | |
|---|---|
| Max-Duration | 40 |
| Lead-Free Process Capability | REFLOW |
| Max-Cycle | 1 |
| Max-Temp | 255 |

Downloaded from Arrow.com.

## Mates With / Use With

### Mates with Part(s)

| Description | Part Number |
|---|---|
| DuraClik Single Row Receptacle Housings | 502351 |
| DuraClik TPA Single Row Receptacle Housings | 505151 |
| DuraClik ISL Single Row Receptacle Housings | 560123 |



Downloaded from Arrow.com.