
SERIES 320 SWITCHES
TACT SWITCHES



SPECIFICATIONS

Contact Rating:	25mA @ 50 VDC
Life Expectancy:	1,000,000 cycles min.
Contact Resistance:	50mΩ, max. initial @ 2-4 VDC, 100mA
Insulation Resistance:	1,000MΩ min.
Dielectric Strength:	>500 VAC rms at sea level
Actuation Force:	135 ± 50 gf
Operating Temperature:	-20°C to 70°C
Travel:	.6mm Typ.

MATERIALS

Housing:	Nylon 4/6
Cover/Cap:	ABS or Polycarbonate
Dome Contact:	Gold over stainless steel
Terminals/Contacts:	Silver plated copper alloy

FEATURES & BENEFITS

- Multiple cap & color options
- High reliability dome technology
- Excellent tactile feedback

APPLICATIONS/MARKETS

- Telecommunications
- Networking
- Computers/servers
- Performance audio
- Instrumentation
- Low power on/off designs
- External hard drives and modems

HOW TO ORDER

CAP STYLE	CIRCUIT	CAP COLOR	ADDITIONAL CAP (Fits over cap styles 320.02 & 320.03 only.)	CAP COLOR
320 320.01 320.02 320.03 320.04 320.22 320.08* 320.09* 320.094* 320.2 320.21	E11 (SPST)	BLK = Black GRY = Grey YEL = Yellow BLU = Blue GRN = Green WHT= White RED = Red	See Cap Section	

Example Ordering Number


320.08–E1-1–YEL


***Note: Assembled using the 320.02 plungered cap.**


Specifications subject to change without notice.

320









SCHEMATIC | P.C. MOUNTING


Downloaded from Arrow.com.


SERIES 320 SWITCHES

TACT SWITCHES

320.01









320.02









320.03









320.04









Downloaded from Arrow.com.

320.22









SCHEMATIC | P.C. MOUNTING

320.2









SCHEMATIC | P.C. MOUNTING

320.21







SCHEMATIC | P.C. MOUNTING

Downloaded from Arrow.com.