

**Part Number :** [191210057](#)


**Product Description :** InsulKrimp Flanged Spade Tongue Terminal for 12-10 AWG Wire, Stud Size 10 (M5), Width 9.53mm, Mylar Tape Carrier

**Series Number :** 19121

**Status :** Active

**Product Category :** Ring and Spade Terminals

**Engineering Part Number :** C-217-10XT



---

## Documents and Resources

### Drawings

[191210057 sd.pdf](#)

### 3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

### Specifications


[PS-19902-009-001.pdf](#)

[PS-19902-015-001.pdf](#)

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant per EU 2015/863

### [Compliance Statements](#)

- EU RoHS
- REACH SVHC
- Low-Halogen

#### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

#### Substances of Interest

- PFAS

#### EU RoHS Certificate of Compliance

#### Additional Product Compliance Information

## Part Details

### General

Status	Active
Category	Ring and Spade Terminals
Series	19121
Description	InsulKrimp Flanged Spade Tongue Terminal for 12-10 AWG Wire, Stud Size 10 (M5), Width 9.53mm, Mylar Tape Carrier
Keyword	Spade Terminal, Spade Terminals
Product Name	InsulKrimp
Style	Spade
Type	Spade Connector, Metric Spade Connector
UPC	800753096080

### Agency

CSA	LR18689
UL	E32244

### Physical

Barrel Type	Closed
Color - Resin	Natural

Flammability	94V-0
Insulation	PVC
Material - Plating Mating	Tin
Net Weight	2.624/g
Packaging Type	Adhesive Tape on Reel
Stud Size	10 (M5)
Wire Insulation Diameter	6.35mm
Wire Size (AWG)	10, 12
Wire Size mm <sup>2</sup>	4.00-6.00

### Solder Process Data

Lead-Free Process Capability	N/A
------------------------------	-----

---

## Application Tooling

### Global

Description	Part Number
Mini-Mac Pneumatic Applicator for Industrial Terminals 26-6 AWG	<u><a href="#">638851500</a></u>

---

This document was generated on Apr 14, 2026