

Small Signal Dual P-Channel MOSFET

FEATURES

- AEC-Q101 Qualified
- Advanced trench cell design
- ESD protected G-S 2kV (HBM)
- RoHS Compliant
- Halogen-free



APPLICATIONS

- Switching circuits
- High-speed line driver
- High-side loadswitch
- Relay driver

PRODUCT SUMMARY			
PARAMETER		VALUE	UNIT
V_{DS}		-60	V
$R_{DS(on)}$ (max)	$V_{GS} = -10V$	6	Ω
	$V_{GS} = -4.5V$	7	
Q_g	$V_{GS} = -4.5V$	1	nC



SOT-363



Note: MSL 1 (Moisture Sensitivity Level) per J-STD-020

ABSOLUTE MAXIMUM RATINGS ($T_A = 25^\circ\text{C}$ unless otherwise noted)			
PARAMETER		SYMBOL	LIMIT
Drain-Source Voltage		V_{DS}	-60
Gate-Source Voltage		V_{GS}	± 20
Continuous Drain Current	$T_A = 25^\circ\text{C}$	I_D	-170
Pulsed Drain Current (Note 1)		I_{DM}	-0.68
Total Power Dissipation	$T_A = 25^\circ\text{C}$	P_D	320
	$T_A = 125^\circ\text{C}$		64
Operating Junction and Storage Temperature Range		T_J, T_{STG}	- 55 to +150

THERMAL PERFORMANCE			
PARAMETER		SYMBOL	LIMIT
Junction to Ambient Thermal Resistance (Note 2)		$R_{\theta JA}$	390

Notes:

1. Pulse Width $\leq 100\mu\text{s}$.
2. Device mounted on an FR4 PCB, single-sided copper, tin-plated and standard footprint.

ELECTRICAL SPECIFICATIONS (T _A = 25°C unless otherwise noted)						
PARAMETER	CONDITIONS	SYMBOL	MIN	TYP	MAX	UNIT
Static (Note 3)						
Drain-Source Breakdown Voltage	V _{GS} = 0V, I _D = -250μA	BV _{DSS}	-60	--	--	V
Gate Threshold Voltage	V _{DS} = V _{GS} , I _D = -250μA	V _{GS(TH)}	-0.8	-1.5	-2.5	V
Gate Body Leakage	V _{GS} = ±20V, V _{DS} = 0V	I _{GSS}	--	--	±10	μA
Zero Gate Voltage Drain Current	V _{DS} = -60V, V _{GS} = 0V	I _{DSS}	--	--	-1	μA
	V _{DS} = -60V, V _{GS} = 0V T _J =125°C		--	--	-100	
Drain-Source On-State Resistance	V _{GS} = -10V, I _D = -170mA	R _{DS(on)}	--	1.9	6	Ω
	V _{GS} = -4.5V, I _D = -160mA		--	2.4	7	
Forward Transconductance	V _{DS} = -10V, I _D = -170mA	g _{fs}	--	434	--	mS
Dynamic (Note 4)						
Total Gate Charge	V _{DS} = -30V, I _D = -170mA, V _{GS} = -10V	Q _g	--	1.9	--	nC
Total Gate Charge	V _{DS} = -30V, I _D = -160mA, V _{GS} = -4.5V	Q _g	--	1	--	nC
Gate-Source Charge		Q _{gs}	--	0.3	--	
Gate-Drain Charge		Q _{gd}	--	0.3	--	
Input Capacitance	V _{DS} = -30V, V _{GS} = 0V, f = 1.0MHz	C _{iss}	--	38.2	--	pF
Output Capacitance		C _{oss}	--	8	--	
Reverse Transfer Capacitance		C _{rss}	--	4.2	--	
Switching (Note 5)						
Turn-On Delay Time	V _{DD} = -30V, R _G = 6.0Ω, I _D = -170mA, V _{GS} = -10V	t _{d(on)}	--	5.5	--	ns
Turn-On Rise Time		t _r	--	2.4	--	
Turn-Off Delay Time		t _{d(off)}	--	39.2	--	
Turn-Off Fall Time		t _f	--	19.6	--	
Source-Drain Diode						
Forward Voltage (Note 3)	I _S = -170mA, V _{GS} = 0V	V _{SD}	--	-0.9	-1.3	V

Notes:

- Pulse test: Pulse Width $\leq 300\mu s$, duty cycle $\leq 2\%$.
- Defined by design. Not subject to production test.
- Switching time is essentially independent of operating temperature.


ORDERING INFORMATION

ORDERING CODE	PACKAGE	PACKING
TQM84KDCU6 RFG	SOT-363	3,000pcs / 7" Reel


CHARACTERISTICS CURVES

($T_A = 25^\circ\text{C}$ unless otherwise noted)


Output Characteristic




Transfer Characteristics




On-Resistance vs. Drain Current




Gate-Source Voltage vs. Gate Charge



On-Resistance vs. Junction Temperature




On-Resistance vs. Gate-Source Voltage




CHARACTERISTICS CURVES

($T_A = 25^\circ\text{C}$ unless otherwise noted)


Capacitance vs. Drain-Source Voltage




BV_{DSS} vs. Junction Temperature




Maximum Safe Operating Area, Junction-to-Ambient



Source-Drain Diode Forward Current vs. Voltage






Normalized Thermal Transient Impedance, Junction-to-Ambient








CHARACTERISTICS CURVES

($T_A = 25^\circ\text{C}$ unless otherwise noted)




PACKAGE OUTLINE DIMENSIONS (Unit: Millimeters)

SOT-363



SUGGESTED PAD LAYOUT



MARKING DIAGRAM

Y = Year Code

M = Month Code for Halogen Free Product

(O=Jan, P=Feb, Q=Mar, R=Apl, S=May, T=Jun,

U=Jul, V=Aug, W=Sep, X=Oct, Y=Nov, Z=Dec)

L = Lot Code (1~9,A~Z)

NOTES: UNLESS OTHERWISE SPECIFIED

1. ALL DIMENSIONS ARE IN MILLIMETERS.
2. DIMENSIONING AND TOLERANCING PER ASME Y14.5M-1994.
3. PACKAGE OUTLINE REFERENCE:
JEITA ED-7500A, EIAJ SC-88.
4. MOLDED PLASTIC BODY DIMENSIONS DO NOT INCLUDE MOLD FLASH, PROTRUSIONS OR GATE BURRS.
5. DWG NO. REF: HQ2SD07-SOT363-097 REV A.

Notice

Specifications of the products displayed herein are subject to change without notice. TSC or anyone on its behalf, assumes no responsibility or liability for any errors or inaccuracies.

Purchasers are solely responsible for the choice, selection, and use of TSC products and TSC assumes no liability for application assistance or the design of Purchasers' products.

Information contained herein is intended to provide a product description only. No license, express or implied, to any intellectual property rights is granted by this document. Except as provided in TSC's terms and conditions of sale for such products, TSC assumes no liability whatsoever, and disclaims any express or implied warranty, relating to sale and/or use of TSC products including liability or warranties relating to fitness for a particular purpose, merchantability, or infringement of any patent, copyright, or other intellectual property right.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications. Customers using or selling these products for use in such applications do so at their own risk and agree to fully indemnify TSC for any damages resulting from such improper use or sale.