



SHEET 1 OF 1




PC MOUNTING








CIRCUIT: SPST ▲





NOTES:
1. ALL DIMENSIONS IN MM
2. GENERAL TOLERANCE: X.X=±0.4
   X.XX=±0.25
3. TERM. NOS. FOR REFERENCE ONLY.
4. RATING: 12VDC, 50mA
▲5. OPERATING FORCE: 160 ± 50 gf
6. TRAVEL: 0.25 +0.2/-0.1 mm
7. CONTACT RESISTANCE: 50 MILLI OHMS MAX. (INITIAL)
8. MECHANICAL/ELECTRICAL LIFE 100,000 CYCLES MIN.
▲9. CONTACT MATERIAL: SILVER
▲10. HOUSING AND ACTUATOR TO MEET UL-94VO STANDARD
11. ▲ DENOTES CRITICAL PARAMETER
▲12. SOLDER PROFILE: 260C MAX FOR 8 SECONDS MAX, PREHEAT
PREHEAT 150C MAX FOR 60 SECONDS
13. OPERATING TEMP: -40°C TO 85°C

REV	PCR NO	DESCRIPTION	DATE	BY
C	24549	REMOVE STEP IN HOUSING, CHANGE TEMP	10/19/20	JM
B	18657	Added Note 11	9/18/09	rc
A	18601	RELEASED FOR PRODUCTION	7/31/09	BLR

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

E•SWITCH®

TITLE TL1105RF160Q94VO

SCALE	DATE	DR	DWG	REV
4:1	7/31/2009	BLR	P010389	C

Downloaded from Arrow.com.