



Pushing Performance
Since 1945

Han 300A crimp module, female KNBN



Image is for illustration purposes only. Please refer to product description.

Part number	09 14 001 3104
Specification	Han 300A crimp module, female KNBN
HARTING eCatalogue	https://b2b.harting.com/09140013104

Version

Termination method	Crimp termination Axial screw termination
Gender	Female
Number of contacts	1
Details	Please order contacts separately.

Technical characteristics

Conductor cross-section	70 ... 120 mm ²
Rated current	300 A
Rated voltage	1,000 V
Rated voltage	1,000 V AC 1,300 V DC
Rated impulse voltage	8 kV
Pollution degree	3
Insulation resistance	>10 ¹⁰ Ω
Limiting temperature	-40 ... +125 °C
Mating cycles	≥500

Material properties

Material (insert)	Polycarbonate (PC)
Colour (insert)	RAL 7032 (pebble grey)
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant



Pushing Performance
Since 1945

Material properties

China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Not contained
Fire protection on railway vehicles	EN 45545-2 (2020-08)
Requirement set with Hazard Levels	R22 (HL 1-3) R23 (HL 1-3)

Specifications and approvals

Specifications	EN 50124-1 IEC 60664-1 IEC 61984
----------------	--

Commercial data

Packaging size	1
Net weight	23.18 g
Country of origin	Germany
European customs tariff number	85366990
GTIN	5713140184466
eCl@ss	27440217 Module for industrial connectors (power/signals)