
RK73H

EU RoHS COMPLIANT

Precision 0.5%, 1% tolerance thick film chip resistor




Features

- Products with lead-free terminations meet EU RoHS requirements. EU RoHS regulation is not intended for Pb-glass contained in electrode, resistor element and glass.
- AEC-Q200 Qualified: 0201 (1H), 0402 (1E), 0603 (1J), 0805 (2A), 1206 (2B), 1210 (2E), 2010 (2H/W2H), 2512 (3A/W3A/W3A2)

Go to: Ordering Information | Applications and Ratings | Environmental Applications |

Introduction of the Derating Curves Based on the Terminal Part Temperature (PDF)


Dimensions and Construction




Type* (Inch Size Code)	Dimensions inches (mm) L	W	c	d	t
1F (01005)	.016±.0008 (0.4±0.02)	.008±.0008 (0.2±0.02)	.004±.001 (0.1±0.03)	.004±.001 (0.11±0.03)	.005±.0008 (0.13±0.02)
1H (0201)	.024±.001 (0.6±0.03)	.012±.001 (0.3±0.03)	.004±.002 (0.1±0.05)	.006±.002 (0.15±0.05)	.009±.001 (0.23±0.03)
1E (0402)	.039 +.004 -.002 (1.0 +0.1 -0.05)	.02±.002 (0.5±0.05)	.008±.004 (0.2±0.1)	.01 +.002 -.004 (0.25 +0.05 -0.1)	.014±.002 (0.35±0.05)
1J (0603)	.063±.008 (1.6±0.2)	.031±.004 (0.8±0.1)	.012±.004 (0.3±0.1)	.012±.004 (0.3±0.1)	.018±.004 (0.45±0.1)
2A (0805)	.079±.008 (2.0±0.2)	.049±.004 (1.25±0.1)	.016±.008 (0.4±0.2)	.012 +.008 -.004 (0.3 +0.2 -0.1)	.02±.004 (0.5±0.1)
2B (1206)	.126±.008 (3.2±0.2)	.063±.008 (1.6±0.2)	.02±.012 (0.5±0.3)	.016 +.008 -.004 (0.4 +0.2 -0.1)	.024±.004 (0.6±0.1)
2E (1210)		.102±.008 (2.6±0.2)			
2H (2010)	.197±.008 (5.0±0.2)	.098±.008 (2.5±0.2)			
W2H (2010)				.026±.006 (0.65±0.15)	
3A (2512)	.248±.008 (6.3±0.2)	.122±.008 (3.1±0.2)		.016 +.008 -.004 (0.4 +0.2 -0.1)	
W3A/W3A2 (2512)				.026±.006 (0.65±0.15)	

* Parentheses indicate EIA package size codes.

Derating Curve



For resistors operated at an ambient temperature of 70°C or above, a power rating shall be derated in accordance with the above derating curve.



For resistors operated at a terminal part temperature of described for each size or above, a power rating shall be derated in accordance with the above derating curve. Please refer to "Introduction of the derating curve based on the terminal part temperature" in the beginning of our catalog before use.

Ordering Information

RK73H	2B	T	TD	1003	F
Type	Size	Termination Material	Packaging	Nominal Resistance	Tolerance
	1F 1H 1E 1J 2A 2B 2E W2H W3A 2H 3A W3A2	T: Sn (1F ~ W3A2) Contact factory for below options: L: SnPb (1E, 1J, 2A, 2B, 2E, 2H, 3A) G: Au (1E ~ 2A: 10Ω ~ 1MΩ)	TX: 01005 only: 4mm width - 1mm pitch plastic embossed TBL: 01005 only: 2mm pitch pressed paper TC: 0201 only: 7" 2mm pitch pressed paper (TC: 10,000 pcs/reel, TCM: 15,000 pcs/reel) TCD: 0201 only: 10" 2mm pitch pressed paper TPD: 0402 only: 10" 2mm pitch plastic embossed TPL: 0402 only: 2mm pitch punch paper TP: 0402, 0603, 0805: 7" 2mm pitch punch paper TD: 0603, 0805, 1206, 1210: 7" 4mm pitch punched paper TDD: 0603, 0805, 1206, 1210: 10" paper tape TE: 0805, 1206, 1210, 2010 & 2512: 7" embossed plastic TED:0805, 1206, 1210, 2010 & 2512: 10" embossed plastic For further information on packaging, please refer to Appendix A	3 significant figures + 1 multiplier "R" indicates decimal on value <100Ω	D: ±0.5% F: ±1%

Order Samples

Sample Order Form

Downloads

Catalog Pages
Introduction of the Derating Curves Based on the Terminal Part Temperature
Terms and Definitions/Environmental Applications
Appendix A - Packaging
Marking and Standard Values
Pad Dimensions
Material Declaration Data Sheet
Lab Kit Data Sheet
Surface Temperature Rise Graph
EU-RoHS * CHINA RoHS
Resistors Caution & Terms
Pb-Free Components Recommended Soldering Information and Profile

Links

P/N Cross Reference
FAQs

Surface Mount Resistors

RK73B
General purpose 2%, 5% tolerance thick film chip resistor

RK73H
Precision 0.5%, 1% tolerance thick film chip resistor

RK73G
Thick film 0.5%, 1% tolerance, 50ppm/°C chip resistor

RK73-RT
Flat chip resistor (Anti-Sulfuration)

WG73
Wide terminal type surge current flat chip resistors (anti surge)

RS73
high reliability chip resistors

RK73G-RT
Flat chip resistor (Ultra precision grade, Anti-Sulfuration

Downloaded from Arrow.com.

Applications and Ratings

Standard Decade Values (E-12, E-24, E-96, E-192)

Part Designation	Power Rating	Rated Ambient Temp.	Rated Terminal Part Temp.	T.C.R. (x10⁻⁶/K)	Resistance Range D±0.5% E-24, E-96	Resistance Range F±1% E-24, E-96*	Maximum Working Voltage	Maximum Overload Voltage	Operating Temperature Range
RK73H1F (01005)	0.03W	70°C	—	±200	—	100kΩ - 2MΩ*	20V	30V	-55°C to +125°C
				±250	—	10Ω - 91kΩ*			
RK73H1H (0201)	0.05W		125°C	±200	10Ω - 1MΩ	10Ω - 10MΩ*	25V	50V	-55°C to +155°C
				±400	—	1.0Ω - 9.1Ω*			
RK73H1E (0402)	0.1W			±100	10Ω - 1MΩ	10Ω - 1MΩ	75V	100V	
				±200	—	1.0Ω - 9.76Ω 1.02MΩ - 10MΩ			
RK73H1J (0603)	0.1W			±100	1.02kΩ - 1MΩ	1.02kΩ - 1MΩ	75V		
				±200	—	1.02MΩ - 10MΩ			
	0.125W			±100	10Ω - 1kΩ	10Ω - 1kΩ			
				±200	—	1.0Ω - 9.76Ω			
RK73H2A (0805)	0.25W			±100	10Ω - 1MΩ	10Ω - 1MΩ	150V	200V	
				±200	—	1.0Ω - 9.76Ω			
				±400	—	1.02MΩ - 10MΩ			
RK73H2B (1206)	0.25W			±100	10Ω - 1MΩ	10Ω - 1MΩ	200V	400V	
				±200	—	1.0Ω - 9.76Ω 1.02MΩ - 5.6MΩ			
				±400	—	5.62MΩ - 10MΩ			
RK73H2E (1210)	0.5W			±100	10Ω - 1MΩ	10Ω - 1MΩ			
				±200	—	1.0Ω - 9.76Ω 1.02MΩ - 5.6MΩ			
					—				
				±400	—	5.62MΩ - 10MΩ			
RK73HW2H/2H (2010)	0.75W			±100	10Ω - 1MΩ	10Ω - 1MΩ			
				±200	—	1.0Ω - 9.76Ω 1.02MΩ - 5.6MΩ			
				±400	—	5.62MΩ - 10MΩ			
RK73HW3A/3A (2512)	1.0W			±100	10Ω - 1MΩ	10Ω - 1MΩ	200V	400V	
				±200	—	1.0Ω - 9.76Ω 1.02MΩ - 5.6MΩ			
				±400	—	5.62MΩ - 10MΩ			
RK73HW3A2 (2512)	2.0W	—	95°C	±100	10Ω - 1MΩ	10Ω - 1MΩ	200V	400V	
				±200	—	1.0Ω - 9.76Ω 1.02MΩ - 5.6MΩ			
				±400	—	5.62MΩ - 10MΩ			

Rated voltage = √Power rating x resistance value or max. working voltage, whichever is lower

* 1F: E-24. 1H: 1.0~9.1, 1M~10MΩ: E-24. If any questions arise whether to use the "Rated Ambient Temperature" or the "Rated Terminal Part Temperature," please give priority to the "Rated Terminal Part Temperature." Prior to use and for more details refer to "Introduction of the derating curves based on the terminal part temperature" in the beginning of the catalog. While using under high power, the temperature of the product may increase depending on the condition of heat dissipation from PCB. Be sure to check the terminal part temperature as well as precautions to use on delivery specification before use.

Environmental Applications

Performance Characteristics

Parameter	Requirement Δ R (%+0.1Ω) Limit	Typical	Test Method
Resistance	Within specified tolerance	—	25°C
T.C.R.	Within specified T.C.R.	—	+25°C/-55°C and +25°C/+125°C
Overload (Short time)	±2%	±1%: 1F ±0.5% Another	Rated Voltage x 2.5 for 5 seconds (1E, 2B, W3A2: Rated Voltage x 2 for 5 seconds)
Resistance to Soldering Heat	±1%: 1F ~ W3A2 (10Ω≤R≤1MΩ); ±3%: 1H ~ W3A2 (R<10Ω, R>1MΩ)	±0.5%: 1F ~ W3A2 (10Ω<R<1MΩ); ±1%: 1H ~ W3A2 (R<10Ω, R>1MΩ)	260°C ± 5°C, 10 seconds ± 1 second
Rapid Change of Temperature	±1%: 1F; ±0.5% Another	±0.5%: 1F; ±0.3% Another	-55°C (30 minutes), +125°C (30 minutes), 100 cycles
Moisture Resistance	±2%: 1J, 2A, 2B ±3%: Another	±0.75%: 1J, 2A, 2B; ±1.5%:1F, ±1%: Another	40°C ± 2°C, 90%-95% RH, 1000 hours, 1.5 hr ON, 0.5 hr OFF cycle
Endurance at 70°C	±2%: 1J, 2A, 2B; ±3%: Another	±0.75%: 1J, 2A, 2B; ±1%: Another	70°C ± 2°C, 1000 hours, 1.5 hr ON, 0.5 hr OFF cycle
High Temperature Exposure	±1%	±0.5%: 1F ±0.3%: Another	+125°C, 1000 hours: 1F; +155°C, 1000 hours: 1E, 1H, 1J, 2A, 2B, 2E, 2H/W2H, 3A/W3A/W3A2

Last Updated on: 2/11/2019

XR73B/XR73H/XR73Z
flat thick film resistors (for embedded substrates)

RS73-RT
high reliability chip resistors (anti-sulfuration)

WK73R
Wide terminal type flat chip resistor

WK73R (Higher Power)
Higher power wide terminal type flat chip resistor

WK73-RT
Wide terminal type flat chip resistor (Anti-Sulfuration)

WK73-RT (Higher Power)
Higher power wide terminal type flat chip resistor (Anti-Sulfuration)

RN73
Ultra precision 0.05%, 0.1%, 1% tolerance thin film chip resistor.
Not Recommended for New Design
Recommended Replacement RN73R

RN73H
High heat resistance, high reliability metal film chip resistor

RN73R
metal film flat chip resistors (high reliability)

HV73
Flat chip resistors for high voltage

HRK73
High Temperature, Gold Termination Thick Film

HV73-RT
Flat chip resistors for high voltage (Anti-Sulfuration)

SHDR
Microwave thin film chip resistors
EOL

HV73V
Flat chip resistors for high voltage (Automotive)

HV73V-RT
Flat chip resistors for high voltage (Automotive– Anti-Sulfuration)

SG73
anti-surge thick film chip resistor

SG73-RT
surge current flat chip resistors (anti-surge, anti-sulfuration)

SG73G
endured pulse power flat chip resistors (ultra precision grade)

SG73P
Anti-surge endured pulse power thick film chip resistor

SG73S
Anti-surge endured surge voltage thick film chip resistor

SG73P-RT
Endured pulse power flat chip resistors (Anti-surge, anti-sulfuration)

SG73S-RT
Endured surge voltage flat chip resistors (Anti-surge, anti-sulfuration)

RK73Z
Zero ohm jumper chip resistor

RF73
Fusing flat chip resistor

Downloaded from Arrow.com.

KOA Speer Electronics 199 Bolivar Drive Bradford, PA 16701 Phone: 814.362.5536 Fax: 814.362.8883

Site Links

Home
Contact
News
KOA international
order catalogs
order samples
KOA net
Customer Satisfaction Survey
Technical Assistance
Career Opportunities

Product Links

Resistors
- Surface Mount Resistors
- Current Sense Resistors
- Melf Type Resistors
- Resistor Arrays
- Integrated Resistor Networks
- Leaded SIP Networks
- Leaded Resistors

Thermal Protection
- Surface Mount Thermal Sensors

Inductors
- Surface Mount Inductors

Capacitors
- Ceramic Chip Capacitors

EMI/EMC FIltering
- Surface Mount Ferrite Beads

Circuit Protection
- Fuses
- Varistors
- Other Chips

Modules
- Low Temperature Co-Fired Ceramic Substrates

KOA Speer Electronics has received our DoC Privacy Shield Certification effective 1/7/2019. Please see our updated Privacy Policy

TS-16949 CERTIFIED
ISO 9001:2008

Downloaded from Arrow.com.