


NOTICE OF PROPRIETARY RIGHTS THIS DOCUMENT CONTAINS CONFIDENTIAL TECHNICAL DATA, INCLUDING TRADE SECRETS, PROPRIETARY TO TIMES MICROWAVE SYSTEMS. DISCLOSURE OF THIS DATA IS EXPRESSLY CONDITIONED UPON YOUR ASSENT THAT ITS USE IS LIMITED TO USE WITHIN YOUR COMPANY ONLY. ANY OTHER USE IS STRICTLY PROHIBITED WITHOUT THE PRIOR WRITTEN CONSENT OF TIMES MICROWAVE SYSTEMS.

SYM	REVISION DESCRIPTION	DFTM	DATE	APPD	DATE
-	RELEASED FOR PRODUCTION	J.C.L.	5/21/01	J.C.L.	5/21/01
A	CHANGED PER CDC #37538	J.D.B.	4/24/13	J.D.B.	4/25/13




CABLE PREPARATION DETAIL
(NOT TO SCALE)





RECOMMENDED PANEL CUTOUT



1.0 PERFORMANCE
1.1 FREQUENCY RANGE: DC-11GHz
1.2 NOMINAL IMPEDANCE: 50 OHMS
1.3 DWV: 2500V RMS @ 60Hz (sea level)
1.4 TEMPERATURE RANGE: -65°C TO +165°C
1.5 PIM: -150 dBc
2.0 MATERIALS: RoHS
2.1 DIELECTRIC: PTFE
2.2 CENTER CONTACT: BeCu
2.3 ALL OTHER METAL PARTS: BRASS
2.4 O-RING: BUNA N
2.5 GASKET: SI RUBBER
2.6 SHRINK SLEEVE: THICK WALL POLYOLEFIN
3.0 FINISHES: BODY: ALBALOY
CONTACT: 30Au/Cu
4.0 MECHANICAL
4.1 INTERFACE PER MIL-STD-348
4.2 NON-CAPTIVE CONTACT

MATL:	UNLESS OTHERWISE SPECIFIED	DFTM. J. C. L.	TIMES MICROWAVE SYSTEMS
USED ON: E	ALL DIMENSIONS ARE IN INCHES MACHINED SURFACES FINISH 32 RMS MAX. REMOVE ALL BURRS .005 MAX. BREAK MACHINE CORNERS .005 MAX. FILLET R. TOLERANCES ON DECIMALS .XX ±.03 .XXX ±.005 ANGLES ± 1° FRACTIONS ± 1/64	DATE 5/21/01 CHKD. J. C. L. DATE 5/21/01 APPD. J. C. L.	TC-400-NFC-BH (A) N FEMALE BULKHEAD FOR LMR-400 CABLE
SCALE: N/A DWG. SIZE A	DO NOT SCALE DRAWING CODE IDENT 68999	DATE 5/21/01	SHT. 1 of 1 SD3190-872 REV. A

Downloaded from Arrow.com.