

MICRO SWITCH
a Honeywell Division

FED. MFG. CODE 91929

SWITCH - BASIC

CATALOG LISTING

V7-7B17D862-201

CW-C6144

CATALOG LISTING
V7-7B17D862-201

PAGE 1 OF 1



ISSUE
3

REVISIONS

A	PR23389	
	TSM	
17	APR 98	
B	0085964	
	SBH	
	30 JAN 12	

CMH

CHECK

17 APR 98

JAF

CHECK

7 APR 98

TSM


PTC/CAD 2D

DRAWN

RELEASE NO. PR-23389

REPLACES


X102349-V7



ANSI Y14.5M-1982 APPLIES

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

THIRD ANGLE PROJECTION



CHARACTERISTICS

OPERATING FORCE	----- 10 OZ MAX
RELEASE FORCE	----- 1 OZ MIN
DIFFERENTIAL TRAVEL	----- .013 MAX
OVERTRAVEL	----- .034 MIN
RELEASE TRAVEL	----- .007 MIN

ELECTRICAL DATA

CONTACT ARRANGEMENT
S P D T

L156 11A 1/3HP 125, 250 OR 277 VAC
1/2A 125 VDC, 1/4A 250 VDC
4A 125 VAC "L"



SCALE NONE

DO NOT SCALE PRINT

UNLESS OTHERWISE SPECIFIED TOLERANCES ARE		
ONE PLACE	(.0)	±.030
TWO PLACE	(.00)	±.015
THREE PLACE	(.000)	±.005
ANGLES		±

WEIGHT