



Part Number : 02081002
Product Description : MLX Crimp Terminal
42024, 20-14 AWG, Bag Tin (Sn)
Series Number : 42024
Status : Active
Product Category : Crimp Terminals
Engineering Number : 42024-1A1L
Packaging Alternative : 02081001 (Reel)




Documents & Resources

Drawings
[002081002_sd.pdf](#)
[PK-36518-381-001.pdf](#)

Specifications
[PS-42022-0001-001.pdf](#)
[TS-42022-0001-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 44
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)7663-DC (21 Jan 2025)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements
- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Crimp Terminals
Series	42024
Description	MLX Crimp Terminal 42024, 20-14 AWG, Bag Tin (Sn)
Application	Power, Wire-to-Board, Wire-to-Wire
Product Name	MLX
UPC	800753615885

Physical

Gender	Female
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.344/g
Packaging Type	Bag
Plating min - Mating	0.508µm
Plating min - Termination	0.508µm
Termination Interface Style	Crimp or Compression
Wire Insulation Diameter	1.52-3.30mm
Wire Size (AWG)	14, 16, 18, 20
Wire Size mm²	N/A

Solder Process Data

Lead-Free Process Capability	N/A
------------------------------	-----

Application Tooling

Global

Description	Part Number
Extraction Tool for MLX 2.13mm Diameter Pin and Socket Crimp Terminals	<u>11010168</u>
PremiumGrade Hand Crimp Tool for MLX Pin and Socket Terminals, 20-14 AWG	<u>638116800</u>

This document was generated on Apr 05, 2025