





LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
AF	50		B	REVISED PER ECR-13-007151	30JUL2013	KH	KR

- 1 FITS 0.81±0.025 X 6.35 [.032±.001 X .250] TAB
REFER TO CP-14251 FOR DETAILS.
- 2 WIRE SIZE: 1.3-2.0MM² [16-14 AWG], STRANDED ONLY.
STRIP LENGTH 7.14 [.281]
- 3 INSULATION SIZE: 4.70 [.185] MAX DIA.
- 4 CONTINUOUS STRIP,SPLICE FREE.



TYPE 6/6 NYLON	BLUE TRANSLUCENT	BRASS	TIN	3-521127-2
MATERIAL	COLOR	MATERIAL	FINISH	PART NUMBER
HOUSING			TERMINAL	

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN JR RUTH 11/4/96		 TE Connectivity								
		CHK MS FEHER 11/4/96										
DIMENSIONS: mm [INCHES]		TOLERANCES, UNLESS OTHERWISE SPECIFIED:		APVD J WORMAN 11/4/96		NAME						
		0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± 0.25 [.010] 4 PLC ± - ANGLES ± -		PRODUCT SPEC 108-2043		RECEPTACLE ASSEMBLY,ULTRA-FAST FLAG, 6.35 [.250] SERIES						
				APPLICATION SPEC 114-2123								
				MATERIAL		FINISH		WEIGHT -		SIZE A2	CAGE CODE 00779	DRAWING NO C=521127
SEE TABLE		SEE TABLE		CUSTOMER DRAWING						SCALE 10:1	SHEET 1 of 1	REV B