





APPROVED: _____

DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	12/13/17	
A		UPDATE DRWING	3/31/21	LH/KL



SPECIFICATIONS:

Material:

Insulator: Nylon66, rated UL 94V-0

Insulator color: White

Contacts: Phosphor Bronze

Plating:

Tin over Copper underplate overall

Electrical:

Voltage rating: 125 V AC/DC.

Current rating: 2A AC/DC.

Contact resistance: 20 mohms max.

Insulation resistance: 1000 Mohms min.

Dielectric withstanding voltage: 800 VAC for 1 minute

Temperature Rating:

-25°C to +85°C

Environmental:

Lead free, RoHS compliant



Positions: 02 thru 15

A = .079 [2.00] x No. of Spaces

B = .079 [2.00] x No. of Spaces + .157 [4.00]

C = .079 [2.00] x No. of Spaces + .122 [3.10]

UNLESS OTHERWISE SPECIFIED
ALL DIMENSIONS ARE INCHES [MM]
TOLERANCES: EXCEPT AS NOTED

INCHES		HOLES	
.X	± .10	Ø.X	± .10
.XX	± .020	Ø.XX	± .015
.XXX	± .015	Ø.XXX	± .010

APPROVALS

DATE

DRAWN

AY

12/13/17

CHECKED

RC1

12/13/17

APPROVED

ADAM
TECH

909 Rahway Avenue,
Union, NJ 07083
Phone: 908-687-5000
Fax: 908-687-5710

TITLE
.079 [2.00] WAFER, PCB TYPE, STRAIGHT
TIN PLATED, INSULATOR COLOR WHITE

SIZE

X

PART NO.

2SH-F-XX-TS-WT

REV.

A

REF:

S00186T

SCALE: NTS

SHEET 1 OF 1