

	1	2	3	4	5	6	7																																																																											
A	① Specifications: Material: Housing: Poly Carbonate(PC) UL94V-2 Contact: Phosphor Bronze with 2 prongs Plating: 6u" gold plated 100u" Nickel under plated Operating temperature: -40°C to +125°C Electrical: Current rating: 250V AC max. at 2A Dielectric: 500V AC Insulation resistance: 500MΩ Termination resistance: 35mΩ max after environmental tests Tensile strength: 20 LBS (89N) min. Durability: 500 mating cycles Complies with FCC68/F ① Wire gauge: 30AWG-24AWG Stranded wire Cable OD size: flat cable 2.5x5.0±0.02mm Wire size: 0.95±0.05mm							A																																																																										
B								B																																																																										
C								C																																																																										
D								D																																																																										
E								E																																																																										
F								F																																																																										
G	RoHS compliant Unit: mm	<table><tr><td>Scale</td><td>Free</td><td></td><td></td><td></td><td></td><td>Date</td><td>Name</td><td>Customer-No.</td></tr><tr><td>TOLERANCE</td><td></td><td></td><td></td><td></td><td>Drawn</td><td>13.06.2016</td><td>Joanna</td><td></td></tr><tr><td>X.X</td><td>±0.20</td><td></td><td></td><td></td><td>Approved</td><td>03.04.2019</td><td>Amy</td><td>ASSMANN WSW-No.</td></tr><tr><td>X.XX</td><td>±0.10</td><td></td><td></td><td></td><td></td><td></td><td></td><td>A-MO 6/4-SF</td></tr><tr><td>X.XXX</td><td>±0.05</td><td></td><td></td><td></td><td></td><td></td><td></td><td></td></tr><tr><td>DIM</td><td>TOL</td><td>①</td><td>Update to new drawing Add cable wire information</td><td>03.04.2019</td><td>Amy</td><td rowspan="3">ASSMANN WSW components</td><td>Drawing-No.</td><td></td></tr><tr><td>X.°</td><td>±3°</td><td>②</td><td>Drawn</td><td>13.06.2016</td><td>Joanna</td><td>ASS 7278 CO</td><td>rev01</td></tr><tr><td>X.X°</td><td>±1.0°</td><td></td><td></td><td></td><td></td><td>Replace</td><td>Sheet</td></tr><tr><td>Angle</td><td>TOL</td><td>Id.</td><td>Modification</td><td>Date</td><td>Name</td><td></td><td></td><td></td></tr></table>	Scale	Free					Date	Name	Customer-No.	TOLERANCE					Drawn	13.06.2016	Joanna		X.X	±0.20				Approved	03.04.2019	Amy	ASSMANN WSW-No.	X.XX	±0.10							A-MO 6/4-SF	X.XXX	±0.05								DIM	TOL	①	Update to new drawing Add cable wire information	03.04.2019	Amy	ASSMANN WSW components	Drawing-No.		X.°	±3°	②	Drawn	13.06.2016	Joanna	ASS 7278 CO	rev01	X.X°	±1.0°					Replace	Sheet	Angle	TOL	Id.	Modification	Date	Name				G
Scale	Free					Date	Name	Customer-No.																																																																										
TOLERANCE					Drawn	13.06.2016	Joanna																																																																											
X.X	±0.20				Approved	03.04.2019	Amy	ASSMANN WSW-No.																																																																										
X.XX	±0.10							A-MO 6/4-SF																																																																										
X.XXX	±0.05																																																																																	
DIM	TOL	①	Update to new drawing Add cable wire information	03.04.2019	Amy	ASSMANN WSW components	Drawing-No.																																																																											
X.°	±3°	②	Drawn	13.06.2016	Joanna		ASS 7278 CO	rev01																																																																										
X.X°	±1.0°						Replace	Sheet																																																																										
Angle	TOL	Id.	Modification	Date	Name																																																																													
H								H																																																																										
	1	2	3	4	5	6	7																																																																											