


2180851-4 Product Details

 Share  Print  Email



 Active

 View 3D PDF

Impact High Density Backplane Connectors

IMP,PWR,3PR,HDR,R-HLD,1X,797-4,N/A

2180851-4 

TE Internal Number: 2180851-4

Product Highlights [View All](#)

- Connector Style = Header
- 8/Power
- 16 Positions
- Header Type = Partially Shrouded
- Board-to-Board Configuration = Right Angle

Pricing & Availability 

Request Sample 

Add to My Part List 

Buy Product through
Distributor 

 Feedback

Documents

Features

Compliance

Please Note:

Use the Product Drawing for all design activity

Product Type Features

PCB Mount Retention Type	Action/Compliant Tail and Screw(s)
PCB Mount Alignment Type	Locating Post(s)

Electrical Characteristics

Operating Voltage Reference	AC rms, DC
Operating Voltage (VAC)	250
Operating Voltage (VDC)	250

Dimensions

Stack Height (mm [in])	14.88 [0.585]
Tail Length (mm [in])	2.5 [0.098]
Length (X-Axis) (mm [in])	23.97 [0.9436]
Width (Z-Axis) (mm [in])	15.00 [0.5905]
Profile Height (Y-Axis) (mm [in])	14.88 [0.5858]
PCB Hole Diameter (mm [in])	0.725 [0.0285]

Body Features

Header Type	Partially Shrouded
-------------	--------------------

Contact Features

Contact Type	Pin
Contact Length (mm [in])	5.70 [0.224], 6.90 [0.271]
Contact Plating, Termination Area, Material	Matte Tin
Contact Plating, Termination Area, Thickness (µm [µin])	2.54 [100]
Contact Base Material	Copper Alloy
Underplate Material	Nickel
Underplate Material Thickness (µm [µin])	1.27 [50.000]

Housing Features

Connector Style	Header
Housing Color	Black
Housing Material	LCP (Liquid Crystal Polymer)

Configuration Features

Connector Contact Configuration (No. of Pos./Type)	8/Power
Number of Positions 	16
Number of Columns	2
Number of Rows 	4
Tail Orientation	In-line

Industry Standards

RoHS/ELV Compliance 	RoHS compliant, ELV compliant
Lead Free Solder Processes 	Not reviewed for lead free solder process
RoHS/ELV Compliance History	Always was RoHS compliant
UL Rating	Recognized
UL File Number	E28476
UL Flammability Rating	UL 94V-0
CSA Certified	Yes

Environmental

Operating Temperature (°C [°F])	-55 – +85 [-67 – +185]
---------------------------------	------------------------

Conditions for Usage

Board-to-Board Configuration	Right Angle
------------------------------	-------------

Operation/Application

Industry Application	Networking (Communications)
----------------------	-----------------------------

Packaging Features

Packaging Method	Tray/Box
------------------	----------

Other

Brand	TE Connectivity
Comment	Parts are shipped with a 2-32 AB Type Self-Tapping Screw, 2057509-2.

Related Products

Not quite the product you're looking for?

[Find Similar Products](#)

[View Part in Product Feature Selector](#)

[Check for Tooling](#)

Corporate Information

[About TE](#)
[Investors](#)
[News Room](#)
[Supplier Portal](#)
[Careers](#)
[Terms & Conditions](#)
[Privacy Policy](#)
[Global Accessibility Statement](#)

Quick Links

[Distributor Inventory](#)
[Product Cross Reference](#)
[Documents & Drawings](#)
[Product Compliance Support Center](#)
[Site Map](#)

Customer Support

[Email or Chat With Us](#)
[Find a Phone Number](#)
[Knowledge Base](#)
[Manage Your Account](#)

Keep Me Informed

