



**Part Number :** [357501010](#)  
**Series Number :** 35750  
**Status :** Active - Proprietary  
**Product Category :** Ring and Spade Terminals




**Specifications**

[PK-35750-001-001.pdf](#)  
[PS-35750-0300-001.pdf](#)

**Product Environment Compliance**

**Compliance**

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Compliant per 2000/53/EC
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

## Part Details

### General

Status	Active - Proprietary
Category	Ring and Spade Terminals
Series	35750
Description	Ring Tongue Terminal for 18-14 AWG (0.75~2.08mm <sup>2</sup> ), Stud Size 8 (M4), Tin Plating
Keyword	Ring Terminal, Ring Terminals
Product Name	N/A
Style	Ring
Type	Ring Terminal
UPC	800753514713

### Agency

UL	E134962
----	---------

### Electrical

Voltage - Maximum	300V AC
-------------------	---------

### Physical

Barrel Type	Open
Insulation	None
Material - Plating Mating	Tin
Net Weight	0.413/g
Packaging Type	Reel
Stud Size	8 (M4)
Temperature Range - Operating	-40° to +105°C
Termination Interface Style	Crimp or Compression
Wire Insulation Diameter	3.20mm max.
Wire Size (AWG)	14, 16, 18

### Solder Process Data

Lead-Free Process Capability	N/A
------------------------------	-----

---

This document was generated on Sep 17, 2025