


N=Number of contacts



Technical Data:

Electrical

Pitch: 7.62mm

Voltage rating: 300V

Current rating: 16 Amps

Contact resistance: 20mΩ(max)

Withstanding Voltage: 2500VAC(1min) Test time=60sec/1pcs

Wire range: 12-26AWG

Wire strip length: 7-8mm

Mechanical:

Torque: 5.0kgf.cm/M3

Operating temperature: -40°C to +105°C

Safety approval:

RoHS Compliance

Part No.:

OSTTJXX0150

No. of Poles

02 2 Poles

03 3 Poles

... ...

24 24 Poles

COLOR

0: Black

2: Red

3: Orange

4: Yellow

5: Green (Standard)

6: Blue

8: Grey

Nonstandard colors
Mins could apply

ITEM	NAME OF PART	MATERIAL	NOTES	Q'TY
5	Screw	Steel / M3.0	Cr3+ plated	1xN
4	Contact	Copper Alloy	Ni plated	1xN
3	Wire guard	Copper Alloy	Tin plated	1xN
2	Cover	PA66 UL94V-0		1
1	Body	PA66 UL94V-0		1
ITEM	NAME OF PART	MATERIAL	NOTES	Q'TY
DWG.	DATE	UNITS: MM	SHEET: 1 OF 1	Tolerance
CHK.	DATE	SCALE: NONE 3:1(1)	REV.: A	X. ±0.50
APP.	DATE	TITLE: OSTTJ SERIES 7.62MM		X.X ±0.30
		PART NO: OSTTJXX0150		X.XX ±0.10
		DWG NO: OSTTJXX0150.DWG		X° ±1°



REV	SIGN	DESCRIPTION	CHK.	DATE
		ON-SHORE TECHNOLOGY, INC.		