


SmartRack 6U Vertical Wall-Mount Rack Bracket

MODEL NUMBER: SRWALLBRKT6U



6U wall-mount bracket allows vertical installation of a 6U rack-mount device up to 200 lb.

Description

The SRWALLBRKT6U SmartRack® 6U Vertical Wall-Mount Rack Bracket is recommended for home offices and small businesses with rack-mount equipment that doesn't need to be secured and no room on the premises for a standard 19-inch server rack.

Made from heavy-duty cold-rolled steel with a durable black powder-coated finish, this 6U wall-mount bracket easily attaches to the wall of your back office or closet with user-supplied hardware. Wall-mounting holes are spaced 16 inches part to match standard wall-stud placement. Or you can install the bracket horizontally beneath a desk or workbench for instant access.

Use the included hardware to attach your 6U rack-mount equipment, such as a network switch or UPS system, to the steel bracket's rails. Its maximum load capacity is 200 lbs (90.7 kgs). Connected equipment hangs flush against the wall, allowing you unrestricted access. The SRWALLBRKT6U is compatible with most EIA-standard 19-inch two-post rack equipment.

Features

6U Wall-Mount Bracket Allows Vertical Mounting in a Closet or Back Office

- Recommended for home offices and small businesses with no room for standard 19 in. rack
- Provides open, unrestricted access to equipment and cabling
- Maximum load capacity of 200 lbs (90.7 kgs)
- Cold-rolled steel construction with black powder-coated finish designed for long life
- Ships fully assembled for quick installation

Attaches to the Wall with User-Supplied Hardware

- Wall-mounting holes spaced 16 in. apart for standard wall stud placement
- Also mounts horizontally beneath a desk or workbench
- Component hangs flush against the wall for unrestricted out-of-the-way access

Compatible with EIA-Standard 19 in. 2-Post Rack Equipment

- Hardware included for mounting 6U rack equipment
- Rails support square-hole mounting

Highlights

- 19-inch wall-mount rack with maximum load capacity of 200 lbs (90.7 kgs)
- Provides open, unrestricted access to equipment and cabling
- Made from cold-rolled steel with black powder-coated finish
- Equipment-mounting hardware included
- Compatible with most EIA-standard 19 in. 2-post rack equipment

Package Includes

- SRWALLBRKT6U SmartRack 6U Vertical Wall-Mount Rack Bracket
- (12) M6 screws
- (12) M6 cup washers
- (12) M6 cage nuts
- Installation guide

Specifications



Powering Business Worldwide

TRIPP LITE
SERIES

OVERVIEW	
UPC Code	037332203212
Device Compatibility	Network Switch; Patch Panel
Rack Type	Bracket
PHYSICAL	
Color	Black
Rack Height	6U
Rack Depth	Shallow
Maximum Device Depth (cm)	121.92
Maximum Device Depth (in.)	48
Maximum Device Depth (mm)	1,219
Maximum Weight Capacity (lbs.)	200
Maximum Weight Capacity (kg)	91
Shipping Dimensions (hwd / in.)	10.83 x 21.85 x 18.31
Shipping Dimensions (hwd / cm)	27.51 x 55.50 x 46.51
Shipping Weight (lbs.)	12.12
Shipping Weight (kg)	5.50
Unit Dimensions (hwd / in.)	11.150 x 19.690 x 11.150
Unit Dimensions (hwd / cm)	28.32 x 50.01 x 28.32
Unit Weight (lbs.)	8.38
Unit Weight (kg)	3.80
Weight Capacity - Stationary (kg)	91
Weight Capacity - Stationary (lbs.)	200
Number of Vertical Mounting Rails	2
FEATURES & SPECIFICATIONS	
Built-in Cable Management	No
Extra Wide	No
Pre-Installed Casters	No
STANDARDS & COMPLIANCE	
Product Compliance	RoHS; EIA/ECA-310-E
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	5-year limited warranty



Powering Business Worldwide

TRIPP LITE
SERIES

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.