

SUBCON-PLUS-PROFIB/PG/SC2 - D-SUB bus connector



2708245

<https://www.phoenixcontact.com/us/products/2708245>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



D-SUB connector, 9-pos., pin, 35° cable outlet, bus system: PROFIBUS DP up to 12 Mbps with PG D-SUB socket for connecting a programming device, termination resistor can be switched on via slide switch, pin assignment: 3, 5, 6, 8; screw connection terminal blocks

Product description

The D-SUB series, SUBCON-PLUS-PROFIB/... was specially designed for use in PROFIBUS systems up to 12 Mbps. Under field conditions, it allows convenient and fast connection of the incoming and outgoing bus cable. The terminating resistor is already integrated in all versions. It can be connected externally by means of a slide switch. At the same time, the outgoing bus segment is switched off. This makes it easy to start up segment by segment while incorrect terminations are avoided. A special feature of the 35° angled connector is that the internal connection unit can be turned round. Whether the cable is to be inserted from the right or left can thus be decided on-site.

Your advantages

- Termination resistor can be connected
- Screw connection
- 35° cable outlet
- Change to the D-SUB orientation through a reversible connection block
- Metal housing for high level of immunity to interference at maximum transmission speed
- Vibration and shock resistance in accordance with EN 50155
- Suitable for all common Fast Connect PROFIBUS cables and RS-485 bus lines

Commercial data

Item number	2708245
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	DN10
Product key	DNC531
Catalog page	Page 446 (C-6-2019)
GTIN	4017918960490
Weight per piece (including packing)	56.3 g
Weight per piece (excluding packing)	34 g
Customs tariff number	85366990
Country of origin	DE

SUBCON-PLUS-PROFIB/PG/SC2 - D-SUB bus connector



2708245

<https://www.phoenixcontact.com/us/products/2708245>

Technical data

Notes

Note on application

Note on application	Only for industrial use
---------------------	-------------------------

Utilization restriction

CCCex note	Use in potentially explosive areas is not permitted in China.
------------	---

Product properties

Product type	Data plug
MTTF	6706 Years (SN 29500 standard, temperature 25°C, operating cycle 21%)
	1817 Years (SN 29500 standard, temperature 40°C, operating cycle 34.25%)
	155 Years (SN 29500 standard, temperature 40°C, operating cycle 100%)
Pin assignment	3, 5, 6, 8

Electrical properties

Maximum power dissipation for nominal condition	0.025 W
Nominal voltage U_N	5 V
Nominal current I_N	100 mA
Transmission medium	Copper

Connection data

D-SUB connection

Connection method	D-SUB connector
-------------------	-----------------

PCB connection

Connection method	Screw connection
Stripping length	5 mm
Conductor cross section, rigid min.	0.14 mm ²
Conductor cross section, rigid max.	1.5 mm ²
Conductor cross section flexible min.	0.14 mm ²
Conductor cross section flexible max.	1 mm ²
Single-wire/terminal point, rigid AWG min.	26
Single-wire/terminal point, rigid AWG max.	16
Min. AWG conductor cross section, flexible	26
Max. AWG conductor cross section, flexible	18

Programming connection

Connection method	D-SUB socket
-------------------	--------------

Interfaces

SUBCON-PLUS-PROFIB/PG/SC2 - D-SUB bus connector




2708245

<https://www.phoenixcontact.com/us/products/2708245>

Bus system	PROFIBUS DP
Signal	PROFIBUS

Dimensions

Dimensional drawing	
Width	16.6 mm
Height	39.4 mm
Length	58 mm

Material specifications

Material (Housing)	ABS (metal-plated)
--------------------	--------------------

Cable/line

External cable diameter	7.6 mm ... 8.4 mm (Incoming bus line)
-------------------------	---------------------------------------

Mechanical properties

Mechanical data	
Insertion/withdrawal cycles	> 200

Mechanical tests

Vibration resistance in accordance with EN 60068-2-6/IEC 60068-2-6	Vibration (operation): 5g, 10...150 Hz, 2.5 h, in XYZ direction
Shock in accordance with EN 60068-2-27/IEC 60068-2-27	Shock (operation): 15g, 11 ms period, half-sine shock pulse

Environmental and real-life conditions

Ambient conditions	
Degree of protection	IP40
Ambient temperature (operation)	-20 °C ... 75 °C
Ambient temperature (storage/transport)	-25 °C ... 80 °C
Altitude	≤ 5000 m (For restrictions, see the manufacturer's declaration for altitude operation)
Permissible humidity (operation)	10 % ... 95 % (non-condensing)
Permissible humidity (storage/transport)	5 % ... 95 % (non-condensing)

Approvals

ATEX	
Identification	II 3 G Ex ec IIC T4 Gc

SUBCON-PLUS-PROFIB/PG/SC2 - D-SUB bus connector



2708245

<https://www.phoenixcontact.com/us/products/2708245>

Certificate	PxCIF15ATEX2744348X
Note	Please follow the special installation instructions in the documentation!

UKEX

Identification	II 3 G Ex ec IIC T4 Gc
Certificate	PxCIMA22UKEX2744348X

Corrosive gas test

Identification	ISA-S71.04-1985 G3 Harsh Group A
----------------	----------------------------------

Standards and regulations

Free from substances that could impair the application of coating	VDMA 24364:2018-05
---	--------------------

SUBCON-PLUS-PROFIB/PG/SC2 - D-SUB bus connector




2708245

<https://www.phoenixcontact.com/us/products/2708245>

Drawings

Dimensional drawing



Dimensional drawing


SUBCON-PLUS-PROFIB/PG/SC2 - D-SUB bus connector



2708245

<https://www.phoenixcontact.com/us/products/2708245>

Schematic diagram




Stripping specifications

SUBCON-PLUS-PROFIB/PG/SC2 - D-SUB bus connector

2708245


<https://www.phoenixcontact.com/us/products/2708245>

Schematic diagram



Right-hand side cable entry

Schematic diagram



Right-hand side cable entry


SUBCON-PLUS-PROFIB/PG/SC2 - D-SUB bus connector



2708245

<https://www.phoenixcontact.com/us/products/2708245>

Schematic diagram




Left-hand side cable entry

SUBCON-PLUS-PROFIB/PG/SC2 - D-SUB bus connector

2708245

<https://www.phoenixcontact.com/us/products/2708245>

Schematic diagram



Function elements


SUBCON-PLUS-PROFIB/PG/SC2 - D-SUB bus connector



2708245

<https://www.phoenixcontact.com/us/products/2708245>

Circuit diagram



Functional diagram of the connector range
SUBCON-PLUS-PROFIB/...

SUBCON-PLUS-PROFIB/PG/SC2 - D-SUB bus connector



2708245

<https://www.phoenixcontact.com/us/products/2708245>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2708245>



cUL Recognized

Approval ID: E238705



UL Recognized

Approval ID: E238705



CSA

Approval ID: 2437602

SUBCON-PLUS-PROFIB/PG/SC2 - D-SUB bus connector



2708245
<https://www.phoenixcontact.com/us/products/2708245>

Classifications

ECLASS

ECLASS-13.0	27440302
-------------	----------

ETIM

ETIM 9.0	EC001132
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

2708245
<https://www.phoenixcontact.com/us/products/2708245>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com