

Product Details for 1046286 - 1

1046286 - 1

Active

SMA/QMA RF Connectors

RoHS Compliant (Statement of Compliance)

Product Highlights:

Connector

Jack

Connector Type = SMA

Terminate To Coaxial Cable

Coaxial Cable Termination Type = Solder

View all Features

Quick Links

Check Pricing & Availability

Search for Tooling

Product Feature Selector

Contact Us About This Product

Documentation & Additional Information	
Product Drawings: OSM STRAIGHT CABLE JACK DIRECT SOLDER ATTACHMENT (PDF, English) Catalog Pages/Data Sheets: None Available Product Specifications: None Available Application Specifications: None Available Instruction Sheets: None Available CAD Files: None Available Additional Information: Product Line Information Related Products: Tooling List all Documents	

Product Features (Please use the Product Drawing for all design activity)	
Product Type Features: Product Type = Connector Gender = Jack Connector Type = SMA Body Style = Straight Body Material = Stainless Steel Body Finish = Gold Center Contact = With Retractable Collar = Without Safety Wire Holes = Without Dielectric Material = TFE Fluorocarbon Comment = Captured Center Contact Mechanical Attachment: Panel Attachment = Without Impedance (?) = 50 Termination Related Features: Coaxial Cable Termination Type = Solder	Body Related Features: Length (mm [in]) = 12.70 [0.500] Contact Related Features: Center Contact Material = Beryllium Copper Center Contact Plating = Gold Configuration Related Features: Coaxial Cable Type (RG/U or Mfg.) = 405 Semi Rigid/2.16 [.085] Industry Standards: Government/Industry Qualification = No RoHS/ELV Compliance = RoHS compliant, ELV compliant Lead Free Solder Processes = Not relevant for lead free process RoHS/ELV Compliance History = Always was RoHS compliant Conditions for Usage: Terminate To = Coaxial Cable Other: Brand = AMP