


987 Series Deadfront Type Terminal Blocks



Rated 600 volts, 50 amps.
Screws: 10-32 steel, nickel plated. Terminal type: tubular clamp. Terminal contacts: copper alloy, nickel plated. Molded material: thermoplastic. Color: natural.



Mfr.'s Type	Terminals		Length (in.)	AWG Range	Features	1-9	10-50
	No.	Spacing (in.)					
0987RZTC02	2	.475	.95	#24-8	Pressure Contact	4.57	3.88
0987RZTC04	4		1.90			9.20	7.82
0987RZTC06	6		2.85			13.19	11.21
0987RZTC08	8		3.80			17.58	14.94
0987RZTC10	10		4.75			21.98	18.68
0987RZTC12	12		5.70			26.24	22.31



Screw and Nut Torque Guide


Recommended tightening torque in inch-pounds.

Nominal Thread Size	for Screw Type Terminal Boards	for Stud & Nut Type Terminal Boards
0-80	.5	—
1-64	—	1.2
2-56	1.6*	—
4-40	—	4*
5-40	4.8*	6*
6-32	9.6*	12*
8-32	16*	20*
10-32	20	25
12-32	25	—
1/4-28	30	38


* Installation torque from MIL-T-55164, general specifications for terminal boards. Some products may have different recommended tightening torques.

Accessories


Kulka® Kliptite™ Quick Connect Tab Terminations



One Side Tabs




Two Side Tabs




Self-locking, quick-connect tabs for Kulka's terminal blocks accept standard female wire terminals. Ideal for vending machines, appliances, or any application that requires a positive, yet quick disconnect termination. Tab material: brass, electro-tin plated.

Mfr.'s Type	Fig.	Tab Width (in.)	For Series	Pkg. Qty.	Per Pkg.
KT19	4	.187	600, 600A & 670A	100	21.67
KT20	5				
KT21	6				
KT34	1	.187	599	100	10.00
KT35	2				
KT46	4	.250	699	100	21.67
KT47	5				
KT48	6				
KT52	1				
KT54	3				
KT55	4	.250	602 & 672	100	21.67
KT57	6				
KT75	6	.250	812	100	21.67
KT81	3				

Solder Terminal Lugs for 600 & 602 Series Terminal Blocks



Style "Y" Lugs



Style "Z" Lugs

Material: Brass Finish: Electro-tin plated

Mfr.'s Type	Fig.	Length "L" (in.)	For Series	Pkg. Qty	Per Pkg. 1-9
600Y	1	.31	600	100	21.66
600Z	2	.62	600		21.66
602Y	1	.49	602		25.00
602Z	2	.60	602		46.67

Jumpers




Fig. 1




Fig. 2




Fig. 3

For single and double row flat mount thermoset terminal blocks. Material: brass Finish: nickel plate.

Mfr.'s Type	Fig.	Terminals	Pkg. Qty.	Per Pkg.	
				1-9	10+
410/411J	1	2	100	10.00	6.67
600J				25.00	8.33
601J				25.00	8.33
602J				25.00	13.33
603J				30.00	15.00

Mfr.'s Type	Fig.	Terminals	Each	
			1-24	25-125
600RJ02	2	2	1.39	1.11
600RJ04		4	1.79	1.43
600RJ06		6	2.80	2.24
600RJS02	3	2	1.84	1.47
600RJS04		4	2.66	2.13
600RJS06		6	3.77	3.02
600RJS08		8	4.39	3.51
600RJS10		10	5.28	4.22
600RJS12		12	5.55	4.44
600RJS14		14	6.09	4.87
600RJS22		22	7.72	6.18
601RJS02	3	2	1.84	1.47
601RJS03		3	2.33	1.86
601RJS04		4	2.66	2.13
601RJS05		5	2.95	2.36
601RJS06		6	3.77	3.02
601RJS07		7	4.00	3.20
601RJS08		8	4.39	3.51
601RJS10		10	5.28	4.22
601RJS12		12	5.55	4.44
601RJS20		20	7.30	5.84
601RJS23		23	8.00	6.40

MARATHON Is Quality.