







RECOMMENDED
CABLE STRIPPING DIM'S



1. CRIMPED FERRULE
HEX. CRIMP SIZE .255"
2. CRIMPED CONTACT PIN
HEX. CRIMP SIZE .068"
3. CRIMP TOOL: A

REV.	DATE	ECR NO.	DESCRIPTION
A	11/20/97	—	ADD CENTER CONTACT
B	04/08/98	—	ADD LMR240 CABLE TO TITLE
C	12/12/06	—	UPDATE DRAWING FORMAT
D	04/01/08	—	REVISE INSULATOR TO PTFE
E	06/23/10	2062	ADD CRIMP DIMENSIONS AND CRIMP TOOL INFORMATION TO DRAWINGS

9	FERRULE	BRASS	NICKEL	1	UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007" .315 – 1.180 = ± 0.015" 1.180 – 4.724 = ± 0.020" DO NOT SCALE DRAWING	APPROVALS	DATE	Amphenol Connex				
8	CONTACT PIN	BRASS	GOLD	1		DRAWN	M.ZHANG					06/23/10
7	WASHER	BRASS	NICKEL	1		CHECKED			PART DESCRIPTION BNC CRIMP PLUG (FOR BELDEN RG-8/X LMR240 CABLE)			
6	SPRING	SK5	NICKEL	1		ISSUED						
5	RETAINER RING	BRASS	NICKEL	1		SHEET	1 OF 1		PART NO. 112533			
4	GASKET	RUBBER	RED	1								
3	INSULATOR	DELIN	NATURAL	1		CAD FILE C:/CONNEX/112533.DWG			DWG. NO. 112533.DWG		REV. E	SIZE A
2	BODY	BRASS	NICKEL	1								
1	SHELL	BRASS	NICKEL	1								
	DESCRIPTION	MATERIAL	FINISH	QTY								