





REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	B	REVISED PER ECO-18-018129	23OCT2019	AP	DS



⌀ 0.05 X Y
ALL PLATED
THRU HOLES



RECOMMENDED PC BOARD
LAYOUT, BACKPLANE,
COMPONENT SIDE SHOWN
SCALE 4:1

- PCB HOLE DIM:
DRILLED HOLE=0.700±0.025mm
FINISHED HOLE=0.60±0.05mm
Cu-THICKNESS=0.0375±0.0125mm
SnPb THICKNESS=0.007±0.003mm
- MATERIAL:
CONTACT AND SHIELD - PHOSPHOR BRONZE
HOUSING - GLASS FILLED POLYESTER
- FINISH: CONTACT AND SHIELD
MATING AREA - 0.76µm MIN GOLD OVER 1.27µm MIN NICKEL
COMPLIANT PIN AREA - 0.5µm MIN BRIGHT TIN
OVER 1.27µm MIN NICKEL
- CONNECTOR MARKED WITH PART NUMBER AND DATE CODE
- DATUMS AND BASIC DIMENSIONS ESTABLISHED BY CUSTOMER
- THE TWO GROUNDS IN EACH COLUMN ARE COMMONED
- CONTACT AREA LUBRICATED WITH BELLCORE
APPROVED LUBRICANT. TECHNICAL REFERENCE:
GR-1217-CORE, ISSUE 1, NOVEMBER 1995
- TE OR TE CONNECTIVITY LOGO IS LOCATED.

THIS PRODUCT HAS NOT
COMPLETED VALIDATION TESTING

		5.30		1469323-1	
		DIM M		PART NUMBER	
THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN DK SCHRUM CHK RA PATTERSON		23JUN2003 23JUN2003	
DIMENSIONS:		APVD		NAME	
mm		-		HEADER ASSEMBLY, 2 PAIR, 2.5mm TAIL, 25mm, HMZD	
		PRODUCT SPEC		-	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APPLICATION SPEC		-	
0 PLC ±		-		SIZE	
1 PLC ±		-		CAGE CODE	
2 PLC ±		-		DRAWING NO	
3 PLC ±		-		RESTRICTED TO	
4 PLC ±		-		A 00779	
ANGLES ±		-		C=1469323	
FINISH		WEIGHT		SCALE	
-		-		8:1	
				SHEET	
		CUSTOMER DRAWING		1 OF	
				REV B	