
REVISION RECORD				
REV	ECN	DESCRIPTION	DRFT	DATE




VIEW A

2EDGVC – 5.0/5.08 – XXP – 1Y –00A (H)

- 2EDGVC (Series No.)
- 5.0/5.08 (Pitch)
- XXP (Poles)
- 1Y (Single Pitch)
- 00A (Color)
- (H) (RoHS)


00A– (Standard)
1. (Grey)
2. (Blue)
3. (Black)
4. (Green)
5. (Orange)
6. (Red)
7. (Transparent)
8. (Yellow)
9. (White)



NOTES1:
UL Standard
1.Rated voltage/current : 300V / 15A
2.Withstanding voltage : AC1600V/1Min.

IEC Standard

Pollution degree	2
Overvoltage category	III
Rate impulse voltage(KV)	4.0KV
Rate voltage(V)	320V
Rate current(A)	20A



PCB LAYOUT

NOTES2:
1.Dimension shall be interpreted per ASME Y14.5–2009
2.Pitch : 5.0/5.08mm, Poles : N=02~24P
3.Operating temperature: −40℃~+105℃
4.Undimensioned tolerances:

Pitch range in mm				Nominal dimension range in mm					– ⌒ ⌭
TO 6	Over 6 TO 10	Over 10 TO 24		TO 30	Over 30 TO 60	Over 60 TO 100	Over 100 TO 150	Over 150	0.1/10 ∠
±0.15	±0.20	±0.30		±0.30	±0.50	±0.70	±1.00	±1.30	±2°

5.RoHS Compliance

DETACHED LISTS

PART NO.: /	DEGSON® 宁波高松电子有限公司 NINGBO DEGSON ELECTRICAL CO., LTD		
APPD: /	NAME: 2EDGVC-5.0/5.08-XXP-1Y-00A(H)		
CHKD: /	TITLE: CUSTOMER DRAWING	REV	D0
DRFT: /	DRAWING NO.: /	SHEET	1/1
THIRD ANGLE PROJECTION	MM (INCH) DO NOT SCALE DRAWING	SCALE	1:1

Downloaded from Arrow.com.