




## Technical Data

05.07.2022

Heat shrinkable tubing adhesive lined - 1.2 m lengths  
TA42 - thin wall, 4:1 shrink ratio

TA42-8/2

Article Number 318-40800



Material: Polyolefin, chemically cross-linked (PO-X)  
Colour: Black (BK)  
Adhesive: Hot melt adhesive

Supplied Ø D min.: 8.0 mm  
Recov. Ø d max.: 2.0 mm  
Wall (WT): 1.20 mm  
Shrink Ratio: 4:1  
Longitudinal Change After Shrinkage: -7% max.  
Min. Shrink Temperature - °C: +110 °C

Test Method

Flammability: flame-retardant, UL 224  
Operating Temperature - °C: -55 °C to +125 °C  
Heat Shock Test: 4h/250°C  
Behaviour at Heat Shock: not cracking, not dripping, not fluid

Dielectric Strength: 20 kV/mm  
Tensile Strength: 15 MPa  
Elongation at break: 350%  
Water Absorption: 0.5 %  
Specifications: ANSI/UL 224

ASTM D876  
ASTM D638  
ASTM D638



We assume no responsibility that the Product will be used for the intended purpose, this is beyond our control. It's up to the customer to check the suitability for a specific application by means of tests. Technical changes and errors reserved