




+ WIRE AND CABLE
HOOK UP WIRE



✓ Active

TE CONNECTIVITY (TE)
22759/33-26-2
Raychem | RC

22759/33-26-2
TE Internal Number: 275829-001
Mil-Spec: M22759/33-26-2
Alias ID: 7-1192042-3

EU RoHS Compliant
EU ELV Compliant

Cable Type Spec 55A
Voltage Rating (V) 600
Insulation Material Radiation-Crosslinked, Modified ETFE
Conductor Material Silver-Coated High Strength Copper Alloy
Wire Size (AWG) 26

↓ PRODUCT DRAWING
English

DOCUMENTATION

Product Drawings

WIRE, RADIATION-CROSSLINKED, MODIFIED, ETFE-INSULATED, SILVER-COATED HIGH STRENGTH COPPER ALLOY, LIGHTWEIGHT

PDF (TIFF AVAILABLE)
English

Product Specifications

Product Specification

Wire And Cable, Electric, Radiation-Crosslinked, Extruded, Modified, Fluoropolymer-Insulated Copper Or Copper Alloy

PDF
English

FEATURES



Please review product documents or [contact us](#) for the latest agency approval information.

Please Note: Use the Product Drawing for all design activity.

Product Type Features

Cable Type Spec 55A
Cable Style Primary
Product Classification Cable - High Performance - Spec 44, 55 & RCW
Product Type Cable

Configuration Features

Number of Strands 19
Number of Conductors 1

Electrical Characteristics

Voltage Rating (V) 600

Body Features

Insulation Material Radiation-Crosslinked, Modified ETFE
Conductor Material Silver-Coated High Strength Copper Alloy
Wire Color Red

Dimensions

Strand Size (AWG) 38
Wire Size (AWG) 26
Wire Size (mm²) .129
Conductor Diameter .5 mm [.02 in]
Overall Outside Diameter .81 mm [.032 in]
Insulation Thickness (in) .005
Wire Diameter .81 mm [.032 in]

Usage Conditions

Operating Temperature Range (°C) -65 – 200

Other

Wire Source United States

PRODUCT COMPLIANCE



Statement of Compliance

Statement of Compliance
PDF

