3M™ Double Coated Urethane Foam Tape 4026, Natural, 1 in x 1 in, 62 mil, 1000 Each/Case

Part Number 4026, 3M Product Number 4026, 3M ID [redacted], UPC 00021200122252

64 (4)

Details Typical Properties Resources Reviews Support Similar Products



Hover over image to zoom in

Change version

Overall Width (Metric)	25.4 mm
Overall Width (Imperial)	1 in
Backing (Carrier) Material	Urethane
Product Color	Off-white
Adhesive Type	Acrylic

Off-white, 0.062(0 in. (1.6 mm) open cell, flexible urethane foam carrier

High shear adhesive with high temperature resistance

Durable foam is ideal for interior mounting applications

View more details

For industrial/occupational use only. Not for consumer sale or use.

Buy Online

3M Hughes	Pack-N-Tape	MSC Industrial
1 Box	1 Box	1 Box

Ask a 3M Expert

Details

Highlights

Off-white, 0.062(0 in. (1.6 mm) open cell, flexible urethane foam carrier

High shear adhesive with high temperature resistance

Durable foam is ideal for interior mounting applications

Ideal for bonding, attaching, and mounting

The foam dampens and prevents vibration

3M™ Double Coated Urethane Foam Tape 4026 is an off-white, 0.062(0 in. (1.6 mm) thick, double coated, open cell urethane foam base that offers high shear strength. It is ideal for bonding, attaching, and mounting.

3M™ Double Coated Urethane Foam Tape 4026 is a 1.92 lb. thick tape manufactured with 3M™ Adhesive 100 for a strong, permanent bond that works well with the open cell foam structure to produce high shear strength. This tape offers an ideal solution for a wide selection of bonding issues on various surfaces. This includes both interior and exterior applications where the tape will be protected from the environment.

This tape features a conformable foam and adhesive combination which provides long-term holding at temperatures up to 220°F (104°C). By using a robust, green plaid, densified kraft paper liner, this tape provides you with reliable performance for industrial applications, such as die cutting and automated dispensers. The liner also helps reduce edge roll and protects the tape from humidity extremes.

Recommended Applications

- General interior and exterior mounting applications where the tape will be protected from the environment
- Mount interior signs and nameplates
- Mounting dispensers and air fresheners
- Bond acoustic panels to walls
- Attach wire clips to wall surfaces
- Mount corner protectors

Enduring Bond

3M™ Adhesive 100 is a firm, acrylic, pressure sensitive adhesive system that features high ultimate bond strength, very good high temperature, solvent resistance and very high shear holding power. Bond strength increases substantially with natural aging. 3M™ Adhesive 100 is well known in the industry for environmental and chemical resistance. For many applications, any one of the products in this grouping will perform satisfactorily when exposed to different chemicals or temperatures. The adhesive offers excellent bond to metal and high surface energy plastics and good temperature and chemical resistance.

What is Double Coated Tape?

In general, double coated tape is composed of a paper, film, or tissue carrier that is coated on both sides with pressure sensitive adhesive. The adhesive is protected by a peel-away liner that can be removed at the time of application or left in place until the joining surfaces are ready to be attached. These tapes can be applied by hand or with a dispenser. Double coated tape dispensers are available in a variety of configurations ranging from manual to fully automatic. Applications for double coated tape are found in construction, fabrication, arts, and hobby.

3M™ Double Coated Urethane Foam Tape 4026 is a 1.92 lb. thick tape manufactured with 3M™ Adhesive 100 for a strong, permanent bond that works well with the open cell foam structure to produce high shear strength. This tape offers an ideal Urethane Foam Tape 4026 is an excellent choice for interior mounting applications where the tape will be protected from the environment

Typical properties

Details	
Adhesive Type	Acrylic
Application	Interior Mirror & Fixture Attachment
Backing (Carrier) Material	Urethane
Brands	3M
Density (Metric)	290 kg/m³
Elongation at Break	100.0 %
Industries	General Industrial
Maximum Operating Temperature (Fahrenheit)	220 °F
Primary Liner	624 Densified Kraft Paper
Primary Liner Color	Green Plaid
Primary Liner Thickness (Imperial)	3 mil
Primary Liner Thickness (Metric)	0.08 mm
Product Color	Off-white
Shelf Life	24 Month
Smallest Saleable Unit	Each
Tensile Strength (Metric)	1240 kg
Units per Case	1.0

Dimensions and Classifications	
Overall Length (Imperial)	1 in
Overall Length (Metric)	0.02 m
Overall Width (Imperial)	1 in
Overall Width (Metric)	25.4 mm

Resources

Other (1) Brochures (1)



3M™ Double Coated Urethane Foam Tape 4026

Other
(PDF, 103KB)

Reviews

Reviews

0.0 (0.0) (0)

Be the first to review this product

Questions

Be the first to ask a question

Ask a 3M Expert

Ask a 3M Expert

Thank you for your interest in 3M Industrial Adhesive & Tape solutions. A 3M Representative will get back to you by phone or email.

All fields are required unless indicated optional.

What can 3M help you with?
Select One

Business Email Address

First Name

Last Name

Job Role
Select One

Phone Number
(e.g. +1 651-733-1110)

Company Name

Company Type
Select One

Country/Region
United States

Company Address
Start typing here to search

City

State/Province
Select One

Zip Code/Postal Code

Industry
Select One

Manufacturing Location
Select One

Application Purpose
Select One

Application Type
Select One

Substrate
Select One

Additional information about your request

Subscribe to 3M marketing communications

3M takes your privacy seriously. 3M and its authorized third parties will use the information you provided in accordance with our Privacy Policy to send you communications which may include promotions, product recommendations and surveys. You may withdraw your consent at any time. If you are a resident outside the U.S. If you do not consent to this use of your personal information, please do not use this system.

SUBMIT

Similar products

	Current product			
	 3M™ Double Coated Urethane Foam Tape 4026 ...	 3M™ Double Coated Urethane Foam Tape 4032	 3M™ Double Coated Urethane Foam Tape 4008	 3M™ Double Coated Urethane Foam Tape 4004
Overall Width (Metric)	25.4 mm	25.4 mm, 12.5 mm, 101.6 mm, 9.5 mm, 203.2 mm, 6.3 mm, 76.2 mm, 6.35 mm, 317.5 mm, 50.8 mm, 304.8 mm, 38.1 mm, 19 mm, 19 mm	50.8 mm, 6.35 mm, 25.4 mm, 38.1 mm, 19.1 mm, 152.4 mm, 19.05 mm, 1 in, 76 mm, 304.8 mm, 101 mm, 1.5 in, 19 mm, 609.6 mm	3.8 cm, 1.3 cm, 50.8 mm, 6.35 mm, 6.5 mm, 76.2 mm
Overall Width (Imperial)	1 in	1 in, 0.5 in, 4 in, 0.37 in, 8 in, 3 in, 0.62 in, 0.25 in, 1.25 in, 24 in, 12 in, 1.5 in, 0.75 in	2 in, 0.25 in, 1 in, 1.5 in, 4 in, 3 in, 0.75 in, 0.4 in, 3 in, 12 in, 72 in, 0.5 in, 0.7 in, 24 in	1 in, 0.5 in, 2 in, 0.25 in, 0.27 in, 3 in
Backing (Carrier) Material	Urethane	Urethane	Urethane	Urethane
Product Color	Off-white	White, Off-white	Off-white, White	Off-white
Adhesive Type	Acrylic	Acrylic	High Temperature Acrylic Adhesive 100	High Temperature Acrylic Adhesive 100, Acrylic

For industrial/occupational use only. Not for consumer sale or use.

3M industrial and occupational products are intended, labeled, and packaged for sale to trained industrial and occupational customers for workplace use. Unless specifically stated otherwise on the applicable product packaging or literature, these products are not intended, labeled, or packaged for sale to or use by consumers (e.g., for home, personal, primary or secondary school, recreational/sporting, or other uses not described in the applicable product packaging or literature), and must be selected and used in compliance with applicable industrial hygiene and safety procedures. 3M is not liable for any use of these products that violates 3M's instructions, warnings, and other limitations, and the user must make any action required under any recall, field action, or other product use notice. Misuse of 3M industrial and occupational products may result in injury, sickness, death, or property damage. For help with product selection and use, consult your on-site safety professional, industrial hygienist, or other subject matter expert.

© 3M 2022. All Rights Reserved.

The brands listed above are trademarks of 3M.