


# NBC-R4AC1/0,5-94G/R4AC1-BU - Patch cable



1413159

<https://www.phoenixcontact.com/us/products/1413159>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Patch cable, degree of protection: IP20, cable length: 0.5 m, number of positions: 8, 10 Gbps, CAT6<sub>A</sub>, connection method: Pierce connection, Ethernet

## Your advantages

- Perfect for industrial applications
- Perfect for office, building, and protected industrial applications (e.g., in control cabinets)
- Compact angle

## Commercial data

Item number	1413159
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	AB11
Product key	ABNABH
Catalog page	Page 387 (C-2-2019)
GTIN	4046356989947
Weight per piece (including packing)	27.5 g
Weight per piece (excluding packing)	27.5 g
Customs tariff number	85444210
Country of origin	PL

# NBC-R4AC1/0,5-94G/R4AC1-BU - Patch cable



1413159

<https://www.phoenixcontact.com/us/products/1413159>

## Technical data

### Product properties

Product type	Data cable preassembled
Sensor type	Ethernet
Number of positions	8
Connection profile	RJ45
Shielded	yes

### Data management status

Article revision	04
------------------	----

### Signaling

Status display	no
Status display present	No

### Electrical properties

Rated voltage (III/3)	72 V (DC)
Nominal voltage $U_N$	48 V
Nominal current $I_N$	0.5 A
Transmission medium	Copper
Transmission speed	10 Gbps

### Mechanical properties

#### Mechanical data

Insertion/withdrawal cycles	200
Insertion force per signal contact	50.00 N
Extraction force per signal contact	30 N

### Material specifications

Contact material	CuSn
Contact surface material	Au
Contact carrier material	PC
Outer sheath, material	PUR

### Connection data

#### Connection technology

Connection method	Pierce connection
-------------------	-------------------

#### Conductor connection

Connection method	Pierce connection
-------------------	-------------------

### Connector

# NBC-R4AC1/0,5-94G/R4AC1-BU - Patch cable



1413159

<https://www.phoenixcontact.com/us/products/1413159>

## Connection 1

Type	Plug straight RJ45
Shielded	yes
Insertion/withdrawal cycles	≥ 750
Degree of protection	IP20

## Connection 2

Type	Plug straight RJ45
Shielded	yes
Insertion/withdrawal cycles	≥ 750
Degree of protection	IP20

## Cable/line

Cable length	0.50 m
Cable type	Ethernet 10 Gbit
Cable structure	2x2xAWG26/7, S/FTP
Outer sheath, material	PUR
External sheath, color	water blue RAL 5021
Conductor structure signal line	6.00 mm +0.2 mm -0.1 mm
AWG signal line	26
Material wire insulation	PE
Shielding	S/FTP
Test voltage, cable	1000 V DC (1 minute)
Cable insulation resistance	2000 MΩ*km (500 V)
Coupling resistance	30.00 mΩ/m (30 MHz)
Halogen-free	according to IEC 60754-1
Flame resistance	IEC 60332-1

## Environmental and real-life conditions

### Ambient conditions

Degree of protection	IP20
	IP20
Ambient temperature (operation)	-25 °C ... 60 °C (RJ45 connector)

## Standards and regulations

Flame resistance	IEC 60332-1
------------------	-------------

# NBC-R4AC1/0,5-94G/R4AC1-BU - Patch cable


1413159

<https://www.phoenixcontact.com/us/products/1413159>



## Drawings

### Schematic diagram



Connector pin assignment plug RJ45

# NBC-R4AC1/0,5-94G/R4AC1-BU - Patch cable



1413159

<https://www.phoenixcontact.com/us/products/1413159>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1413159>



**EAC**

Approval ID: 19060508

# NBC-R4AC1/0,5-94G/R4AC1-BU - Patch cable



1413159

<https://www.phoenixcontact.com/us/products/1413159>

## Classifications

### ECLASS

ECLASS-11.0	27060308
ECLASS-12.0	27060308
ECLASS-13.0	27060307

### ETIM

ETIM 9.0	EC001855
----------	----------

### UNSPSC

UNSPSC 21.0	26121600
-------------	----------

# NBC-R4AC1/0,5-94G/R4AC1-BU - Patch cable



1413159

<https://www.phoenixcontact.com/us/products/1413159>

## Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2024 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)