




	10	9	8	7	6	5	4	3	2	1																																																																																																																																																																																																											
F	RESISTANCE VS TEMPERATURE CHARACTERISTICS										F																																																																																																																																																																																																										
E	<table><tr><td>TEMP (□)</td><td>Rmin(KΩ)</td><td>Rnom(KΩ)</td><td>Rmax(KΩ)</td></tr><tr><td>-40</td><td>224.87</td><td>234.42</td><td>244.35</td></tr><tr><td>-35</td><td>169.65</td><td>176.35</td><td>183.30</td></tr><tr><td>-30</td><td>129.00</td><td>133.73</td><td>138.61</td></tr><tr><td>-25</td><td>98.843</td><td>102.19</td><td>105.64</td></tr><tr><td>-20</td><td>76.292</td><td>78.668</td><td>81.111</td></tr><tr><td>-15</td><td>59.302</td><td>60.994</td><td>62.728</td></tr><tr><td>-10</td><td>46.409</td><td>47.615</td><td>48.848</td></tr><tr><td>-05</td><td>36.558</td><td>37.418</td><td>38.294</td></tr><tr><td>00</td><td>28.980</td><td>29.592</td><td>30.214</td></tr><tr><td>05</td><td>23.114</td><td>23.548</td><td>23.988</td></tr><tr><td>10</td><td>18.543</td><td>18.850</td><td>19.159</td></tr><tr><td>15</td><td>14.961</td><td>15.176</td><td>15.391</td></tr><tr><td>20</td><td>12.138</td><td>12.286</td><td>12.434</td></tr><tr><td>25</td><td>9.900</td><td>10.000</td><td>10.100</td></tr><tr><td>30</td><td>8.084</td><td>8.182</td><td>8.280</td></tr><tr><td>35</td><td>6.635</td><td>6.728</td><td>6.823</td></tr><tr><td>40</td><td>5.472</td><td>5.560</td><td>5.649</td></tr><tr><td>45</td><td>4.535</td><td>4.617</td><td>4.699</td></tr><tr><td>50</td><td>3.776</td><td>3.851</td><td>3.927</td></tr><tr><td>55</td><td>3.158</td><td>3.227</td><td>3.296</td></tr><tr><td>60</td><td>2.653</td><td>2.715</td><td>2.778</td></tr><tr><td>65</td><td>2.238</td><td>2.295</td><td>2.352</td></tr><tr><td>70</td><td>1.896</td><td>1.947</td><td>1.999</td></tr><tr><td>75</td><td>1.613</td><td>1.659</td><td>1.706</td></tr><tr><td>80</td><td>1.377</td><td>1.419</td><td>1.461</td></tr><tr><td>85</td><td>1.181</td><td>1.218</td><td>1.256</td></tr><tr><td>90</td><td>1.016</td><td>1.050</td><td>1.084</td></tr><tr><td>95</td><td>0.8773</td><td>0.9076</td><td>0.9390</td></tr><tr><td>100</td><td>0.7602</td><td>0.7876</td><td>0.8160</td></tr><tr><td>105</td><td>0.6610</td><td>0.6858</td><td>0.7115</td></tr><tr><td>110</td><td>0.5766</td><td>0.5991</td><td>0.6223</td></tr><tr><td>115</td><td>0.5047</td><td>0.5250</td><td>0.5461</td></tr><tr><td>120</td><td>0.4431</td><td>0.4615</td><td>0.4807</td></tr><tr><td>125</td><td>0.3902</td><td>0.4069</td><td>0.4244</td></tr><tr><td>130</td><td>0.3446</td><td>0.3599</td><td>0.3758</td></tr><tr><td>135</td><td>0.3053</td><td>0.3191</td><td>0.3336</td></tr><tr><td>140</td><td>0.2711</td><td>0.2838</td><td>0.2970</td></tr><tr><td>145</td><td>0.2415</td><td>0.2531</td><td>0.2652</td></tr><tr><td>150</td><td>0.2156</td><td>0.2262</td><td>0.2373</td></tr></table>				TEMP (□)	Rmin(KΩ)	Rnom(KΩ)	Rmax(KΩ)	-40	224.87	234.42	244.35	-35	169.65	176.35	183.30	-30	129.00	133.73	138.61	-25	98.843	102.19	105.64	-20	76.292	78.668	81.111	-15	59.302	60.994	62.728	-10	46.409	47.615	48.848	-05	36.558	37.418	38.294	00	28.980	29.592	30.214	05	23.114	23.548	23.988	10	18.543	18.850	19.159	15	14.961	15.176	15.391	20	12.138	12.286	12.434	25	9.900	10.000	10.100	30	8.084	8.182	8.280	35	6.635	6.728	6.823	40	5.472	5.560	5.649	45	4.535	4.617	4.699	50	3.776	3.851	3.927	55	3.158	3.227	3.296	60	2.653	2.715	2.778	65	2.238	2.295	2.352	70	1.896	1.947	1.999	75	1.613	1.659	1.706	80	1.377	1.419	1.461	85	1.181	1.218	1.256	90	1.016	1.050	1.084	95	0.8773	0.9076	0.9390	100	0.7602	0.7876	0.8160	105	0.6610	0.6858	0.7115	110	0.5766	0.5991	0.6223	115	0.5047	0.5250	0.5461	120	0.4431	0.4615	0.4807	125	0.3902	0.4069	0.4244	130	0.3446	0.3599	0.3758	135	0.3053	0.3191	0.3336	140	0.2711	0.2838	0.2970	145	0.2415	0.2531	0.2652	150	0.2156	0.2262	0.2373	<table><tr><td>TEMP (□)</td><td>Rmin(KΩ)</td><td>Rnom(KΩ)</td><td>Rmax(KΩ)</td></tr><tr><td>155</td><td>0.1931</td><td>0.2028</td><td>0.2129</td></tr><tr><td>160</td><td>0.1733</td><td>0.1822</td><td>0.1915</td></tr><tr><td>165</td><td>0.1559</td><td>0.1640</td><td>0.1726</td></tr><tr><td>170</td><td>0.1405</td><td>0.1481</td><td>0.1560</td></tr><tr><td>175</td><td>0.1270</td><td>0.1339</td><td>0.1412</td></tr><tr><td>180</td><td>0.1150</td><td>0.1214</td><td>0.1281</td></tr><tr><td>185</td><td>0.1044</td><td>0.1103</td><td>0.1165</td></tr><tr><td>190</td><td>0.0949</td><td>0.1004</td><td>0.1062</td></tr><tr><td>195</td><td>0.0865</td><td>0.0915</td><td>0.0969</td></tr><tr><td>200</td><td>0.0789</td><td>0.0836</td><td>0.0886</td></tr></table>				TEMP (□)	Rmin(KΩ)	Rnom(KΩ)	Rmax(KΩ)	155	0.1931	0.2028	0.2129	160	0.1733	0.1822	0.1915	165	0.1559	0.1640	0.1726	170	0.1405	0.1481	0.1560	175	0.1270	0.1339	0.1412	180	0.1150	0.1214	0.1281	185	0.1044	0.1103	0.1165	190	0.0949	0.1004	0.1062	195	0.0865	0.0915	0.0969	200	0.0789	0.0836	0.0886	E
TEMP (□)	Rmin(KΩ)	Rnom(KΩ)	Rmax(KΩ)																																																																																																																																																																																																																		
-40	224.87	234.42	244.35																																																																																																																																																																																																																		
-35	169.65	176.35	183.30																																																																																																																																																																																																																		
-30	129.00	133.73	138.61																																																																																																																																																																																																																		
-25	98.843	102.19	105.64																																																																																																																																																																																																																		
-20	76.292	78.668	81.111																																																																																																																																																																																																																		
-15	59.302	60.994	62.728																																																																																																																																																																																																																		
-10	46.409	47.615	48.848																																																																																																																																																																																																																		
-05	36.558	37.418	38.294																																																																																																																																																																																																																		
00	28.980	29.592	30.214																																																																																																																																																																																																																		
05	23.114	23.548	23.988																																																																																																																																																																																																																		
10	18.543	18.850	19.159																																																																																																																																																																																																																		
15	14.961	15.176	15.391																																																																																																																																																																																																																		
20	12.138	12.286	12.434																																																																																																																																																																																																																		
25	9.900	10.000	10.100																																																																																																																																																																																																																		
30	8.084	8.182	8.280																																																																																																																																																																																																																		
35	6.635	6.728	6.823																																																																																																																																																																																																																		
40	5.472	5.560	5.649																																																																																																																																																																																																																		
45	4.535	4.617	4.699																																																																																																																																																																																																																		
50	3.776	3.851	3.927																																																																																																																																																																																																																		
55	3.158	3.227	3.296																																																																																																																																																																																																																		
60	2.653	2.715	2.778																																																																																																																																																																																																																		
65	2.238	2.295	2.352																																																																																																																																																																																																																		
70	1.896	1.947	1.999																																																																																																																																																																																																																		
75	1.613	1.659	1.706																																																																																																																																																																																																																		
80	1.377	1.419	1.461																																																																																																																																																																																																																		
85	1.181	1.218	1.256																																																																																																																																																																																																																		
90	1.016	1.050	1.084																																																																																																																																																																																																																		
95	0.8773	0.9076	0.9390																																																																																																																																																																																																																		
100	0.7602	0.7876	0.8160																																																																																																																																																																																																																		
105	0.6610	0.6858	0.7115																																																																																																																																																																																																																		
110	0.5766	0.5991	0.6223																																																																																																																																																																																																																		
115	0.5047	0.5250	0.5461																																																																																																																																																																																																																		
120	0.4431	0.4615	0.4807																																																																																																																																																																																																																		
125	0.3902	0.4069	0.4244																																																																																																																																																																																																																		
130	0.3446	0.3599	0.3758																																																																																																																																																																																																																		
135	0.3053	0.3191	0.3336																																																																																																																																																																																																																		
140	0.2711	0.2838	0.2970																																																																																																																																																																																																																		
145	0.2415	0.2531	0.2652																																																																																																																																																																																																																		
150	0.2156	0.2262	0.2373																																																																																																																																																																																																																		
TEMP (□)	Rmin(KΩ)	Rnom(KΩ)	Rmax(KΩ)																																																																																																																																																																																																																		
155	0.1931	0.2028	0.2129																																																																																																																																																																																																																		
160	0.1733	0.1822	0.1915																																																																																																																																																																																																																		
165	0.1559	0.1640	0.1726																																																																																																																																																																																																																		
170	0.1405	0.1481	0.1560																																																																																																																																																																																																																		
175	0.1270	0.1339	0.1412																																																																																																																																																																																																																		
180	0.1150	0.1214	0.1281																																																																																																																																																																																																																		
185	0.1044	0.1103	0.1165																																																																																																																																																																																																																		
190	0.0949	0.1004	0.1062																																																																																																																																																																																																																		
195	0.0865	0.0915	0.0969																																																																																																																																																																																																																		
200	0.0789	0.0836	0.0886																																																																																																																																																																																																																		
D											D																																																																																																																																																																																																										
C											C																																																																																																																																																																																																										
B											B																																																																																																																																																																																																										
A	<table><tr><td>FUNCTIONAL SYMBOLS</td><td colspan="2">THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION</td><td colspan="8" rowspan="5"> molex GLASS NTC PROBE A -10K±1%,B3600,L100 PRODUCT CUSTOMER DRAWING <table><tr><td>DOCUMENT NUMBER</td><td>DOC TYPE</td><td>DOC PART</td><td>REVISION</td></tr><tr><td>2185343607</td><td>PSD</td><td>000</td><td>A2</td></tr></table></td></tr><tr><td> FA = 0 FE = 0 FP = 0 </td><td>DIMENSION UNITS mm</td><td>SCALE NTS</td><td colspan="2">CURRENT REV DESC:</td></tr><tr><td colspan="3">GENERAL TOLERANCES (UNLESS SPECIFIED)</td><td colspan="2">EC NO: 727818 DRWN: NANDAK CHK'D: RBBHASKAR APPR: RBBHASKAR</td></tr><tr><td colspan="3">ANGULAR TOL ± ° 4 PLACES ± 3 PLACES ± 2 PLACES ± 1 PLACE ± 0 PLACES ±</td><td colspan="2">INITIAL REVISION: DRWN: RAVIKM APPR: RBBHASKAR</td></tr><tr><td>DIVISIONAL SYMBOLS</td><td colspan="2">THIRD ANGLE PROJECTION</td><td>DRAWING A3-SIZE</td><td>SERIES 218534</td><td>MATERIAL NUMBER 2185343607</td><td>CUSTOMER GENERAL MARKET</td><td colspan="3">SHEET NUMBER 2 OF 2</td></tr><tr><td colspan="4">DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS</td><td colspan="7"></td></tr></table>										FUNCTIONAL SYMBOLS	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION		molex GLASS NTC PROBE A -10K±1%,B3600,L100 PRODUCT CUSTOMER DRAWING <table><tr><td>DOCUMENT NUMBER</td><td>DOC TYPE</td><td>DOC PART</td><td>REVISION</td></tr><tr><td>2185343607</td><td>PSD</td><td>000</td><td>A2</td></tr></table>								DOCUMENT NUMBER	DOC TYPE	DOC PART	REVISION	2185343607	PSD	000	A2	FA = 0 FE = 0 FP = 0	DIMENSION UNITS mm	SCALE NTS	CURRENT REV DESC:		GENERAL TOLERANCES (UNLESS SPECIFIED)			EC NO: 727818 DRWN: NANDAK CHK'D: RBBHASKAR APPR: RBBHASKAR		ANGULAR TOL ± ° 4 PLACES ± 3 PLACES ± 2 PLACES ± 1 PLACE ± 0 PLACES ±			INITIAL REVISION: DRWN: RAVIKM APPR: RBBHASKAR		DIVISIONAL SYMBOLS	THIRD ANGLE PROJECTION		DRAWING A3-SIZE	SERIES 218534	MATERIAL NUMBER 2185343607	CUSTOMER GENERAL MARKET	SHEET NUMBER 2 OF 2			DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS											A																																																																																																																																																			
FUNCTIONAL SYMBOLS	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION		molex GLASS NTC PROBE A -10K±1%,B3600,L100 PRODUCT CUSTOMER DRAWING <table><tr><td>DOCUMENT NUMBER</td><td>DOC TYPE</td><td>DOC PART</td><td>REVISION</td></tr><tr><td>2185343607</td><td>PSD</td><td>000</td><td>A2</td></tr></table>								DOCUMENT NUMBER	DOC TYPE	DOC PART									REVISION	2185343607	PSD	000	A2																																																																																																																																																																																											
DOCUMENT NUMBER	DOC TYPE	DOC PART									REVISION																																																																																																																																																																																																										
2185343607	PSD	000									A2																																																																																																																																																																																																										
FA = 0 FE = 0 FP = 0	DIMENSION UNITS mm	SCALE NTS									CURRENT REV DESC:																																																																																																																																																																																																										
GENERAL TOLERANCES (UNLESS SPECIFIED)											EC NO: 727818 DRWN: NANDAK CHK'D: RBBHASKAR APPR: RBBHASKAR																																																																																																																																																																																																										
ANGULAR TOL ± ° 4 PLACES ± 3 PLACES ± 2 PLACES ± 1 PLACE ± 0 PLACES ±			INITIAL REVISION: DRWN: RAVIKM APPR: RBBHASKAR																																																																																																																																																																																																																		
DIVISIONAL SYMBOLS	THIRD ANGLE PROJECTION		DRAWING A3-SIZE	SERIES 218534	MATERIAL NUMBER 2185343607	CUSTOMER GENERAL MARKET	SHEET NUMBER 2 OF 2																																																																																																																																																																																																														
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS																																																																																																																																																																																																																					
<table><tr><td>DOCUMENT STATUS</td><td>P1</td><td>RELEASE DATE</td><td>2022/11/15</td><td>05:51:02</td></tr></table>											DOCUMENT STATUS	P1	RELEASE DATE	2022/11/15	05:51:02	7	6	5	4	3	2	1																																																																																																																																																																																															
DOCUMENT STATUS	P1	RELEASE DATE	2022/11/15	05:51:02																																																																																																																																																																																																																	

Downloaded from Arrow.com