


PRODUCT NUMBER	PITCH
HWxx50x200J0G	5.08 mm






N=Number of Poles
 Dim P=(N-1)×5.08
 Dim L=N×5.08
 Dim A=N×5.08+0.5
 Dim B=(N-1)×5.08+10.16
 Dim C=(N-1)×5.08+15.24

Poles	Dim L	Dim P	Dim A	Dim B	Dim C
2P-6P	±0.15	±0.10	±0.15	±0.10	±0.15
7P-12P	±0.20	±0.15	±0.20	±0.15	±0.20
13P-18P	±0.25	±0.20	±0.25	±0.20	±0.25
19P-24P	±0.30	±0.25	±0.30	±0.25	±0.30

PART NO.: HW xx 50 x 2 00J0 G

Solid block 0 Black (RAL9005)
 No. of poles 2 Red (RAL3001/D)
 02 2 poles 3 Orange(RAL2011/P)
 03 3 poles 4 Yellow(RAL1018/A)
 ... 5 Green(RAL6018/T)
 24 24 poles 6 Blue (RAL5015/A)
 8 Grey(RAL7035/D)
 9 White(RAL1102)
 C Green(RAL6018/U)

RoHS compliant
 (lead<4%)
 In copper Alloy




Material:

- Item①Top body:Thermoplastic (UL94V-0)
- Item②Bottom body:Thermoplastic (UL94V-0)
- Item③Terminal lever:Thermoplastic (UL94V-0) Orange(RAL2011/P)
- Item④Spring clamp:Stainless Steel
- Item⑤Female contact:PhBz (CuSn) Tin plated
- Item⑥Flange screw:Steel M2.5 plated zinc

Electrical cULus

- Voltage rating:300V
- Current rating:10A
- Solid wire(AWG):12-26
- Stranded wire(AWG):12-26
- Wire strip length:8-9mm
- Withstanding Voltage:1.6KV
- Operating temperature: -40°C to +115°C
- Safety Approval: 



mat'l. code				surface	tolerance	projection	product family		
ltr ecn no dr date				ASME Y14.5 ✓	ASME Y14.5		TERMINAL BLOCK		
				tolerances unless otherwise specified		MM	title		
				angles	X.±0.5		TERMINAL BLOCK		
				0.015"	X.X±0.3		SPRING CLAMP, PLUGGABLE PLUG, WITH FLANGE		
				X°±1°	X.XX±0.1	scale	CONTACT ON DOWN SIDE		
				dr	EVIN ZHONG 051514		dwg no		sheet 1 of 1 size
				enr	EVIN ZHONG 051514		HWxx50x200J0G		A4
				chr	HANKE FENG 051514				
				appd	SHI JUN 051514		type		CUSTOMER Drawing
sheet index	revision	A							
	sheet	1							