



Part Number : [1204061029](#)

Product Description : M12 Data, D-Coded, M12 Push-Pull Ultra-Lock 2.0 Double Ended Cordset, 4 Poles, M12 Ultra-Lock 2.0 Male (Straight) to Male (90°), 2x2x24 AWG, Teal Shielded TPU WSOR Cable, 1.0m (3.28') Length

Series Number : 120406

Status : Active

Product Category : Circular Industrial Cordsets

Engineering Part Number : EYYAS6216M010


Documents and Resources

Drawings

[1204061029 sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2023)3788-DC (14 Jun 2023)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration

- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

UKCA - Declaration of Conformity

CE - Declaration of Conformity

Part Details

General

Status	Active
Category	Circular Industrial Cordsets
Series	120406
Description	M12 Data, D-Coded, M12 Push-Pull Ultra-Lock 2.0 Double Ended Cordset, 4 Poles, M12 Ultra-Lock 2.0 Male (Straight) to Male (90°), 2x2x24 AWG, Teal Shielded TPU WSOR Cable, 1.0m (3.28') Length
IP Rating	IP67
Performance Category	5e
Product Name	M12 Data Push-Pull,Ultra-Lock 2.0 (M12),Industrial Ethernet
Protocol	EtherNet
Type	Double Ended
UPC	196823153600

Agency

UL	E361772
----	---------

Electrical

Current - Maximum per Contact	4A
Voltage - Maximum	250V

Physical

Cable Diameter	6.50mm (.256")
Cable Length	1.0m (3.28')
Color - Cable Jacket	Teal
Connector End A	M12 Data Push-Pull
Connector End B	M12 Data Push-Pull
Coupling Style	Push-Pull
Gender	Male-Male
Keyway	D-Coded
LED Indicator	None
Material - Cable Jacket	TPU
Material - Connector Body	TPC
Material - Contact	Brass
Material - Coupling Nut	N/A
Material - Plating Mating	Gold
Net Weight	91.255/g
Orientation	90° to Straight
Poles	4
Temperature Range - Operating	-40° to +85°C
Wire/Cable Type	UL 21215
Wire Size (AWG)	24

This document was generated on Apr 28, 2026