

GNSS L1/L2/L5/L6 SMD SAW DIPLEXER



AFII-SW-0095-Q

Request Samples




Check Inventory



1.5 x 1.1 x 0.38 mm
RoHS Compliant
MSL Level = 1

Description

This AEC-Q200 compliant SAW diplexer delivers comprehensive multi-band GNSS coverage for next-generation positioning systems. Supporting L1 alongside combined L2/L5/L6 bands in an ultra-compact 1.5 x 1.1 x 0.38 mm package. Supporting L1 alongside L2/L5/L6 bands with low insertion loss of 1.3 dB (L1) and 1.7 dB (L2/L5/L6), it delivers excellent band separation with 29 dB typical out-of-band rejection. Rated for high-power +25 dBm operation across -40 to +105 °C, this RoHS-compliant MSL Level 1 component enables centimeter-level accuracy for automotive telematics, RTK systems, autonomous vehicles, and precision agriculture where robust multi-frequency performance in harsh environments is essential.



Features

- AEC-Q200 GNSS L1/L2/L5/L6 SAW Diplexer
- Compact Size: 1.5 x 1.1 x 0.38 mm
- Insertion Loss: 1.3 dB (L1) / 1.7 dB (L2/L5/L6)
- Out-of-Band Rejection: 29 dB (Typ.)
- Maximum Input Power: +25 dBm
- Extended Temperature -40 to +105 °C
- [RoHS Compliant](#) | [MSL Level 1](#)

Applications

- High-Precision GNSS Modules
- RTK Systems
- Automotive Transportation & Telematics
- Asset Tracking / Fleet Management
- UAVs, Robotics & Autonomous Vehicles
- Micro-Mobility Solutions
- Precision Agriculture

Ordering Information

Part Number	Description
AFII-SW-0095-Q	GNSS L1/L2/L5/L6 SMD SAW DIPLEXER on Cut Tape
AFII-SW-0095-Q-T	GNSS L1/L2/L5/L6 SMD SAW DIPLEXER on Tape & Reel
AFII-SW-0095-Q -EVB	GNSS L1/L2/L5/L6 SMD SAW DIPLEXER EVB

Note: Other options not listed may be available upon request via [Abracon online support](#)



12117 Bee Caves Rd, Bldg-3, Suite 200 Bee
Cave, TX 78738
Phone: 512-371-6159 | Fax: 512-351-8858
For terms and conditions of sales, please visit:
www.abracon.com

REVISED: 01-09-26

ABRACON IS
ISO9001-2015
CERTIFIED

GNSS L1/L2/L5/L6 SMD SAW DIPLEXER



AFII-SW-0095-Q

Request Samples




Check Inventory



1.5 x 1.1 x 0.38 mm
RoHS Compliant
MSL Level = 1

GNSS Frequency Bands Covered

GPS	L1 1575.42MHz	L2 1227.6MHz	L5 1176.45MHz	
	■	■	■	
GLONASS	G1 1598.06-1609.31MHz	G2 1242.93-1251.68MHz	G3 1202.025MHz	
	■	■	■	
Galileo	E1 1575.42MHz	E5a 1176.45MHz	E5b 1201.5MHz	E6 1278.75MHz
	■	■	■	■
BeiDou	B1 1561MHz	B2 1207.14MHz	B3 1268.52MHz	
	■	■	■	
QZSS	L1 1575.42MHz	L2 1227.6MHz	L5 1176.45MHz	L6 1278.75MHz
	■	■	■	■
IRNSS/NAVIC			L5 1176.45MHz	
			■	
SBAS	L1/E1/B1 1575.42MHz		L5/B2a/E5a 1176.45MHz	
	■		■	



Frequency allocation: GNSS systems, upper L bands and lower L bands



12117 Bee Caves Rd, Bldg-3, Suite 200 Bee
Cave, TX 78738
Phone: 512-371-6159 | Fax: 512-351-8858
For terms and conditions of sales, please visit:
www.abracon.com

REVISED: 01-09-26

ABRACON IS
ISO9001-2015
CERTIFIED

GNSS L1/L2/L5/L6 SMD SAW DIPLEXER



AFII-SW-0095-Q

Request Samples



Check Inventory



1.5 x 1.1 x 0.38 mm
RoHS Compliant
MSL Level = 1

Electrical Specification

Parameters	Minimum	Typical	Maximum	Units	Notes
Frequency	1525		1610.485	MHz	GNSS L1/G1/B1/L
VSWR	-	1.7	2.0		1525 ~ 1610.485 MHz
Insertion Loss ⁽¹⁾ (L)	-	1.7	2.0	dB	1525 ~ 1559 MHz
Insertion Loss ⁽¹⁾ (B1)	-	1.3	1.9		1559.052 ~ 1563.144 MHz
Insertion Loss ⁽¹⁾ (L1)	-	1.3	1.8		1565.19 ~ 1585.65 MHz
Insertion Loss ⁽¹⁾ (G1)	-	1.4	2.0		1592.953 ~ 1610.485 MHz
Amplitude Ripple ⁽¹⁾	-	0.5	2.0	dB	1525 ~ 1610.485 MHz
Group Delay Ripple ⁽¹⁾ (L)	-	6.4	16	ns	1525 ~ 1559 MHz
Group Delay Ripple ⁽¹⁾ (B1)	-	1.2	7		1559.052 ~ 1563.144MHz
Group Delay Ripple ⁽¹⁾ (L1)	-	4.6	7		1565.19 ~ 1585.65MHz
Group Delay Ripple ⁽¹⁾ (G1)	-	6	10		1592.953 ~ 1610.485MHz
Attenuation (Reference level from 0 dB)	30	45	-	dB	100 ~ 885 MHz
	28	31	-		885 ~ 1100 MHz
	28	30	-		1100 ~ 1125 MHz
	27	29	-		1164.45 ~ 1299 MHz
	26.5	27	-		1325 ~ 1462.9 MHz
	15	23	-		1660 ~ 1680 MHz
	19	25	-		1680 ~ 2400 MHz
	23	25	-		2400 ~ 2700 MHz
	23	25	-		2700 ~ 3300 MHz
	21	23	-		3300 ~ 4200 MHz
	20	22	-		4200 ~ 5000 MHz
	19	21	-		5000 ~ 5925 MHz
	15	20	-		5925 ~ 7125 MHz
Source Impedance ⁽²⁾ (single ended)	-	50	-	Ω	3.6nH
Load Impedance ⁽²⁾ (single ended)	-	50	-	Ω	GNSS L1:5.6 nH GNSS L2/L5/L6:7.5 nH
RF Power Dissipation	-	25	-	dBm	-

Notes: (1) Averaged values of linear S-Parameters at +25°C

(2) A matching network is necessary (refer to the Measurement Circuits section)



12117 Bee Caves Rd, Bldg-3, Suite 200 Bee
Cave, TX 78738
Phone: 512-371-6159 | Fax: 512-351-8858
For terms and conditions of sales, please visit:
www.abracon.com

REVISED: 01-09-26

ABRACON IS
ISO9001-2015
CERTIFIED

GNSS L1/L2/L5/L6 SMD SAW DIPLEXER



AFII-SW-0095-Q

Request Samples



Check Inventory



1.5 x 1.1 x 0.38 mm
RoHS Compliant
MSL Level = 1

Parameters	Minimum	Typical	Maximum	Units	Notes
Frequency	1164.45	-	1299	MHz	GNSS L2/B2/L5/E5/L6
VSWR	-	1.9	2.0	:1	1164.45 ~ 1299 MHz
Insertion Loss ⁽¹⁾ (L5)	-	2.3	2.6	dB	1164.45 ~ 1188.45 MHz
Insertion Loss ⁽¹⁾ (B2b/E5b)	-	1.7	2.0		1196.91 ~ 1217.37 MHz
Insertion Loss ⁽¹⁾ (L2)	-	1.7	2.0		1217.37 ~ 1237.83 MHz
Insertion Loss ⁽¹⁾ (L6)	-	2.3	2.6		1237.83 ~ 1299 MHz
Amplitude Ripple	-	0.7	2.0	dB	11164 ~ 1299 MHz
Group Delay Ripple ⁽¹⁾ (L5)	-	17	28	ns	1164.45 ~ 1188.45 MHz
Group Delay Ripple ⁽¹⁾ (B2b/E5b)	-	3	5		1196.91 ~ 1217.37 MHz
Group Delay Ripple ⁽¹⁾ (L2)	-	5	8		1217.37 ~ 1237.83 MHz
Group Delay Ripple ⁽¹⁾ (L6)	-	26	42		1237.83 ~ 1299 MHz
Attenuation (Reference level from 0 dB)	30	44	-	dB	100 ~ 885 MHz
	25	28	-		885 ~ 1100 MHz
	15	27	-		1100 ~ 1125 MHz
	27	29	-		1325 ~ 1462.9 MHz
	27	29	-		1525 ~ 1610.485 MHz
	27	33	-		1660 ~ 1680 MHz
	26	28	-		1680 ~ 2400 MHz
	23	27	-		2400 ~ 2700 MHz
	23	25	-		2700 ~ 3300 MHz
	22	23	-		3300 ~ 4200 MHz
	19	21	-		4200 ~ 5000 MHz
	18	20	-		5000 ~ 5925 MHz
Source Impedance ⁽²⁾ (single ended)	-	50	-	Ω	3.6nH
Load Impedance ⁽²⁾ (single ended)	-	50	-	Ω	GNSS L1:5.6 nH GNSS L2/L5/L6:7.5 nH
RF Power Dissipation	-	25	-	dBm	-

Notes: (1) Averaged values of linear S-Parameters at +25°C

(2) A matching network is necessary (refer to the Measurement Circuits section)




12117 Bee Caves Rd, Bldg-3, Suite 200 Bee
 Cave, TX 78738
 Phone: 512-371-6159 | Fax: 512-351-8858
 For terms and conditions of sales, please visit:
www.abracon.com

REVISED: 01-09-26

ABRACON IS
 ISO9001-2015
 CERTIFIED

GNSS L1/L2/L5/L6 SMD SAW DIPLEXER



AFII-SW-0095-Q

Request Samples



Check Inventory



1.5 x 1.1 x 0.38 mm

RoHS Compliant

MSL Level = 1

Mechanical Specification

Parameters	Specifications
Filter Dimension	1.5 x 1.1 x 0.38 mm
Mounting Type	Surface Mount
Additional Resources	Download STEP File, Package Drawing, 3D PDF

Environmental Specification

Parameters	Specifications
Operating Temperature Range	-40°C ~ +105°C
Storage Temperature Range	-40°C ~ +105°C
ESD Voltage (HBM)	> 100 V
ESD Voltage (MM)	> 50 V
MSL level	1
RoHS Compliant	Yes



12117 Bee Caves Rd, Bldg-3, Suite 200 Bee
Cave, TX 78738
Phone: 512-371-6159 | Fax: 512-351-8858
For terms and conditions of sales, please visit:
www.abracon.com

REVISED: 01-09-26

ABRACON IS
ISO9001-2015
CERTIFIED

GNSS L1/L2/L5/L6 SMD SAW DIPLEXER



AFII-SW-0095-Q

Request Samples




Check Inventory




1.5 x 1.1 x 0.38 mm
RoHS Compliant
MSL Level = 1


Product Dimensions



TOP VIEW





FRONT VIEW



BOTTOM VIEW

RECOMMENDED LAND PATTERN



Unit : mm

Pin No.	Description
2	Common Input
4	L5 Output
6	L1 Output
1, 3, 5	Ground



12117 Bee Caves Rd, Bldg-3, Suite 200 Bee
Cave, TX 78738
Phone: 512-371-6159 | Fax: 512-351-8858
For terms and conditions of sales, please visit:
www.abracon.com

REVISED: 01-09-26

ABRACON IS
ISO9001-2015
CERTIFIED

GNSS L1/L2/L5/L6 SMD SAW DIPLEXER



AFII-SW-0095-Q

Request Samples



Check Inventory




1.5 x 1.1 x 0.38 mm

RoHS Compliant

MSL Level = 1

Measurement Circuit



Port	Matching Component
Input (Pin 2)	X1: 3.6 nH
GNSS L1 Output (Pin 6)	X3: 5.6 nH
GNSS L2/L5/L6 Output (Pin 4)	X2: 7.5 nH



12117 Bee Caves Rd, Bldg-3, Suite 200 Bee
Cave, TX 78738
Phone: 512-371-6159 | Fax: 512-351-8858
For terms and conditions of sales, please visit:
www.abracon.com

REVISED: 01-09-26

ABRACON IS
ISO9001-2015
CERTIFIED

GNSS L1/L2/L5/L6 SMD SAW DIPLEXER



AFII-SW-0095-Q

Request Samples



Check Inventory




1.5 x 1.1 x 0.38 mm

RoHS Compliant


MSL Level = 1

Frequency Characteristics

Insertion Loss 1000 – 1800 MHz



Insertion Loss 10 - 6000MHz




12117 Bee Caves Rd, Bldg-3, Suite 200 Bee
Cave, TX 78738
Phone: 512-371-6159 | Fax: 512-351-8858
For terms and conditions of sales, please visit:
www.abracon.com

REVISED: 01-09-26

ABRACON IS
ISO9001-2015
CERTIFIED

GNSS L1/L2/L5/L6 SMD SAW DIPLEXER



AFII-SW-0095-Q

Request Samples




Check Inventory




1.5 x 1.1 x 0.38 mm
RoHS Compliant
MSL Level = 1

Return Loss 1000 – 1800 MHz



VSWR 1000 - 1800MHz



12117 Bee Caves Rd, Bldg-3, Suite 200 Bee
Cave, TX 78738
Phone: 512-371-6159 | Fax: 512-351-8858
For terms and conditions of sales, please visit:
www.abracon.com

REVISED: 01-09-26

ABRACON IS
ISO9001-2015
CERTIFIED

GNSS L1/L2/L5/L6 SMD SAW DIPLEXER



AFII-SW-0095-Q

Request Samples



Check Inventory




1.5 x 1.1 x 0.38 mm


RoHS Compliant

MSL Level = 1

Group Delay (L1)



Group Delay (L2/L5/L6)



12117 Bee Caves Rd, Bldg-3, Suite 200 Bee
Cave, TX 78738
Phone: 512-371-6159 | Fax: 512-351-8858
For terms and conditions of sales, please visit:
www.abracon.com

REVISED: 01-09-26

ABRACON IS
ISO9001-2015
CERTIFIED

GNSS L1/L2/L5/L6 SMD SAW DIPLEXER



AFII-SW-0095-Q

Request Samples




Check Inventory



1.5 x 1.1 x 0.38 mm
RoHS Compliant
MSL Level = 1

Isolation 1000 - 1800MHz



12117 Bee Caves Rd, Bldg-3, Suite 200 Bee
Cave, TX 78738
Phone: 512-371-6159 | Fax: 512-351-8858
For terms and conditions of sales, please visit:
www.abracon.com

REVISED: 01-09-26

ABRACON IS
ISO9001-2015
CERTIFIED

GNSS L1/L2/L5/L6 SMD SAW DIPLEXER



AFII-SW-0095-Q

Request Samples



Check Inventory




1.5 x 1.1 x 0.38 mm

RoHS Compliant


MSL Level = 1

Smith Chart (L1 & L2/L5/L6)

Smith chart S11 (1525~1610MHz)



Smith chart S11 (1164~1299MHz)



12117 Bee Caves Rd, Bldg-3, Suite 200 Bee Cave, TX 78738
Phone: 512-371-6159 | Fax: 512-351-8858
For terms and conditions of sales, please visit:
www.abracon.com

REVISED: 01-09-26

ABRACON IS
ISO9001-2015
CERTIFIED

GNSS L1/L2/L5/L6 SMD SAW DIPLEXER



AFII-SW-0095-Q

Request Samples



Check Inventory



1.5 x 1.1 x 0.38 mm
RoHS Compliant
MSL Level = 1

Reflow Profile [JEDEC J-STD-020]




Table 1

SnPb Eutectic Process

Classification Temperatures (T_c)

Package Thickness	Volume mm^3 <350	Volume mm^3 ≥ 350
<2.5mm	235°C	220°C
$\geq 2.5\text{mm}$	220°C	220°C

Table 2

Pb-Free Process

Classification Temperatures (T_c)

Package Thickness	Volume mm^3 <350	Volume mm^3 350-2000	Volume mm^3 >2000
<1.6mm	260°C	260°C	260°C
1.6mm - 2.5mm	260°C	250°C	245°C
>2.5mm	250°C	245°C	245°C

Profile Feature	Sn-Pb Eutectic Assembly	Pb-Free Assembly
Preheat / soak		
Temperature minimum (T_{smin})	100°C	150°C
Temperature maximum (T_{smax})	150°C	180°C
Time (T_{smin} to T_{smax}) (t_s)	60 – 120 sec.	60 – 90 sec.
Average ramp-up rate (T_{smax} to T_p)	3°C/sec. max	3°C/sec. max
Liquidous temperature (T_L)	183°C	220°C
Time at Liquidous (T_L)	60 – 150 sec.	50 – 80 sec.
Peak package body temperature (T_p)*	See Table 1	See Table 2
Time (T_p)* within 5°C of the specified classification temperature (T_c)	20 sec.	20 ~ 40 sec.
Ramp-down rate (T_p to T_{smax})	6°C/sec. max	6°C/sec. max
Time 25°C to peak temperature	6 min. max	8 min. max
Reflow cycles	2 max	2 max

*Tolerance for peak profile temperature (T_p) is defined as a supplier minimum and a user maximum.

**Tolerance for time at peak profile temperature (t_p) is defined as a supplier minimum and a user maximum.



12117 Bee Caves Rd, Bldg-3, Suite 200 Bee
Cave, TX 78738
Phone: 512-371-6159 | Fax: 512-351-8858
For terms and conditions of sales, please visit:
www.abracon.com

REVISED: 01-09-26

ABRACON IS
ISO9001-2015
CERTIFIED

GNSS L1/L2/L5/L6 SMD SAW DIPLEXER



AFII-SW-0095-Q

Request Samples




Check Inventory



1.5 x 1.1 x 0.38 mm
RoHS Compliant
MSL Level = 1

Packaging

Tape & Reel Dimension



Carrier Tape Specifications (mm)

Do	D1	E1	P0	P2	F	P1	W	A0	B0	K0	Reel Qty
1.5 ± 0.1/-0	0.60 ± 0.05	1.75 ± 0.1	4.0 ± 0.1	2.0 ± 0.05	3.5 ± 0.05	4.0 ± 0.1	8.0 ± 0.2	1.35 ± 0.1	1.65 ± 0.1	0.75 ± 0.05	5,000

Reel Specifications (mm)

A	W1	N	C	D
178.0 ± 1.0	9.5 ± 0.5	60 ± 0.5	13.5 ± 0.5	21 ± 0.8

ATTENTION: Abracon LLC's products are Commercial-Off-The-Shelf ("COTS"), which are designed, intended, and validated for use in commercial, industrial, and automotive applications. The customer is responsible for testing and verifying the performance of an Abracon solution to meet their system-level requirements.



12117 Bee Caves Rd, Bldg-3, Suite 200 Bee
Cave, TX 78738
Phone: 512-371-6159 | Fax: 512-351-8858
For terms and conditions of sales, please visit:
www.abracon.com

REVISED: 01-09-26

ABRACON IS
ISO9001-2015
CERTIFIED