
Part Number : 464371212
Product Description : 7.50mm Pitch EXTreme Ten60Power Right-Angle Plug Assembly with Guide Pins, 8 AC Power Circuits
Series Number : 46437
Status : Active
Product Category : Board-to-Board Connectors



Documents and Resources

Drawings

464371212_sd.pdf

PK-46437-001-000.pdf

Symbol and Footprint (Multi-Format)

Specifications

PS-46436-100-001.pdf

464361000-TS-000.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 44; 34; 33
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

Downloaded from Arrow.com.

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Board-to-Board Connectors
Series	46437
Description	7.50mm Pitch EXTreme Ten60Power Right-Angle Plug Assembly with Guide Pins, 8 AC Power Circuits
Application	Board-to-Board, Power
Comments	See PS-46436-100 for details
Component Type	PCB Header, Plug
Keyword	Ten60
Product Name	EXTreme Ten60Power
UPC	884982625198

Agency

CSA	LR19980
UL	E29179

Electrical

Current - Maximum per Contact	2.5A, 60.0A
Voltage - Maximum	600V AC / 250V DC

Physical

Breakaway	No

Downloaded from Arrow.com.

Circuits (Loaded)	7
Circuits (maximum)	7
Color - Resin	Black
Durability (mating cycles max)	200
First Mate / Last Break	No
Flammability	94V-0
Glow-Wire Capable	No
Guide to Mating Part	Side, Yes
Keying to Mating Part	No
Lock to Mating Part	No
Mated Height	18.00mm
Material - Metal	Copper
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic
Net Weight	26.138/g
Number of Rows	1
Orientation	Right Angle
Packaging Type	Tray
PCB Locator	Yes
PCB Retention	No
PCB Thickness - Recommended	1.58mm
PC Tail Length	2.84mm
Pitch - Mating Interface	7.50mm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
(p)ower-(s)ignal Configuration	7p - 0s
Shrouded	No
Stackable	No
Temperature Range - Operating	-40° to +105°C
Termination Interface Style	Through Hole

Solder Process Data

Max-Duration	40
Lead-Free Process Capability	SMC&WAVE

Downloaded from Arrow.com.

Max-Cycle	3
Max-Temp	260

Mates With / Use With

Mates with Part(s)

Description	Part Number
EXTreme Ten60Power Right-Angle Receptacle with Side Guides, 8 AC Power Circuits	464361212

Downloaded from Arrow.com.