

MHQ0603P39NHT000



Applications	Commercial Grade
Feature	Multilayer
	Non-Magnetic Core (Dielectric Ceramic)
	Super High Q
Series   Type	MHQ-P
Status	Production
Brand	TDK



Size	
Length(L)	0.65mm ±0.05mm
Width(W)	0.35mm ±0.05mm
Thickness   Height	0.35mm ±0.05mm
Recommended Land Pattern (A)	0.25mm Nom.
Recommended Land Pattern (B)	0.30mm Nom.
Recommended Land Pattern (C)	0.30mm Nom.

Electrical Characteristics	
Inductance	39nH ±3% at 300MHz
Rated Current	160mA
DC Resistance [Typ.]	2.24Ω
DC Resistance [Max.]	3Ω
Self Resonant Frequency [Min.]	1.6GHz
Self Resonant Frequency [Typ.]	2.3GHz
Q [Min.]	14 at 300MHz
Q [Typ.]	





Other	
Operating Temp. Range (Including Self-Temp. Rise)	-55 to 125°C
Soldering Method	Reflow
AEC-Q200	NO
Packing	Punched (Paper)Taping [180mm Reel, Tape width 8mm]
Package Quantity	15000pcs
Weight	0.0002g

! Images are for reference only and show exemplary products.  
! This PDF document was created based on the data listed on the TDK Corporation website.  
! All specifications are subject to change without notice.

MHQ0603P39NHT000



## Characteristic Graphs(This is reference data, and does not guarantee the products characteristics.)





# Associated Images

