Part Number : 643201318
Product Description : .635mm, 1.50mm, CMC Receptacle, 48 Circuits, Left Wire Output, Gray Coding, Mat Sealed
Series Number : 64320
Status : Active
Product Category : Connector Housings



Documents and Resources

Drawings

643201318_sd.pdf

3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

Specifications

AS-64319-002-001.pdf

AS-64319-002-CH-001.pdf

AS-64319-002-FR-001.pdf

AS-64319-002-SP-001.pdf

AS-98420-002-001.pdf

AS-98420-002-CH-001.pdf

AS-98420-002-FR-001.pdf

AS-98420-002-SP-001.pdf

PK-64320-001-001.pdf

PS-64319-001-001.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant
China RoHS	Not Relevant
EU ELV	Compliant per 2000/53/EC
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains

Downloaded from Arrow.com.

	Dodecamethylcyclohexasiloxane; Decamethylcyclopentasiloxane; Octamethylcyclotetrasiloxane per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements
- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Connector Housings
Series	64320
Description	.635mm, 1.50mm, CMC Receptacle, 48 Circuits, Left Wire Output, Gray Coding, Mat Sealed
Application	Automotive, Wire-to-Board
Comments	Current tested on a 5 terminals loaded connector, current for temperature increase of 40°C; Current max = 6.0A for 0.635mm Terminal (0.75mm^2 wire) and 12.0A for 1.50mm Terminal (2.00mm^2 wire)
Component Type	Housing
More Detailed Tech Information	Sealed, high-density, modular

Downloaded from Arrow.com.

	connecting system for Power Train and Body Electronics applications in cars, trucks, busses
Product Name	CMC
UPC	883906129804

Physical

Circuits Detail	8 x 1.5mm & 40 x 0.635mm terminals
Circuits (maximum)	48
Color - Resin	Gray
Gender	Receptacle
Glow-Wire Capable	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Resin	Polyester
Net Weight	35.700/g
Number of Rows	4
Packaging Type	Carton
Panel Mount	No
Pitch - Mating Interface	2.54mm, 3.70mm
Polarized to Mating Part	Yes
Sealed	Sealed
Stackable	No
Temperature Range - Operating	-40° to +125°C
Terminal Size	0.635, 1.5, 2.8

Solder Process Data

Lead-Free Process Capability	N/A

Mates With / Use With

Mates with Part(s)

Description	Part Number
CMC Header 154 Circuits, 3-Bay	347630001

Downloaded from Arrow.com.

(Bay-X 48 Circuits; Bay-Y 53 Circuits; Bay-Z 53 Circuits) Compliant Pin, Press-fit Style	

Use with Part(s)

Description	Part Number
Wire Cap for Mat Sealed CMC Receptacle, 28 Circuits and 48 Circuits	643201301
CMC 0.635mm Blind Cavity Plug	643251010
CMC 1.50mm Blind Cavity Plug	643251023
0.635mm CMC CP Female Terminals	64322
1.50mm CMC CP Female Terminals	64323

Application Tooling

Global

Description	Part Number
Continuity Test Pen Assembly	638121100
Unlocking Tool for CMC and CMX Receptacle Connector	638241200

Downloaded from Arrow.com.