



CONNECTORS

AUTOMOTIVE, TRUCK, BUS, & OFF-ROAD HEADERS



✓ Active

## TE CONNECTIVITY (TE) RECP ASM

STRIKE

[SRK15-MDB-32A-001](#)

TE Internal Number: SRK15-MDB-32A-001

EU RoHS Compliant

EU ELV Compliant

**Number of Positions** 32

**Centerline (Pitch)** 3.4 mm [.134 in]

**Sealable** Yes

**Mounting Orientation** Vertical/180°

**Number of Rows** 4

 **PRODUCT DRAWING**  
English

 **3D PDF**

## DOCUMENTATION

Product Drawings

**RECP ASM**

PDF

English

CAD Files

**3D PDF**

PDF

3D

**Customer View Model**

2D\_DXF.ZIP

English

#### **Customer View Model**

3D\_IGS.ZIP

English

#### **Customer View Model**

3D\_STP.ZIP

English

---

## **FEATURES**



Please review product documents or [contact us](#) for the latest agency approval information.

Please Note: Use the Product Drawing for all design activity.

---

### Product Type Features

**Sealable** Yes

**Connector & Contact Terminates To** Printed Circuit Board

**Shielded** Yes

**Hybrid Header** Yes

---

### Configuration Features

**Number of Positions** 32

**Number of Rows** 4

**Number of Sections** 1

---

### Electrical Characteristics

**Operating Voltage (VAC)** 250

**Operating Voltage (VDC)** 250

---

### Body Features

**Color** Black

---

### Contact Features

**Pin Diameter (mm)** 1, 1.5

**Pin Diameter (in)** .039, .059

**Interface Plating** Tin (Sn)

---

### Termination Features

**Termination Method** Through Hole - Solder

---

### Mechanical Attachment

**Panel Mount Retention** Without  
**PCB Mount Alignment** With  
**Mounting Orientation** Vertical/180°  
**Mounting Holes** With  
**Locking Interface** With  
**PCB Mount Retention Type** Solder Tails  
**PCB Mount Retention** With

---

Housing Features

**Centerline (Pitch)** 3.4 mm [.134 in]

---

Dimensions

**Width** 39.88 mm [1.57 in]

**Length** 82.04 mm [3.23 in]

---

Usage Conditions

**Operating Temperature Range** -55 – 125 °C [-67 – 257 °F]

**Operating Temperature (Max) (°C)** 100, 105, 110, 120, 125, 65, 70, 75, 80, 85, 90

**Operating Temperature (Max) (°F)** 149, 158, 167, 176, 185, 194, 212, 221, 230, 248, 257

---

Operation/Application

**Circuit Application** Signal

---

Industry Standards

**UL Flammability Rating** None

---

Packaging Features

**Packaging Quantity** 1

**Packaging Type** Box

---

## PRODUCT COMPLIANCE



Statement of Compliance

### Statement of Compliance

PDF

---