

## LINDA-Z2T25

Double asymmetric beam for aisle and shelf lighting



### SPECIFICATION:


Dimensions	25.7 x 1140.0
Height	5.3 mm
ROHS compliant	yes 

### MATERIALS:

Component	Type	Material	Colour	Finish	Length (mm)
LINDA-Z2T25	Linear lens	PMMA			

### ORDERING INFORMATION:

Component	Qty in box	MOQ	MPQ	Box weight (kg)
F16858_LINDA-Z2T25	150	150	150	12.2
» Box size: 1200x160x120 mm				




See also our general installation guide: [www.ledil.com/installation\\_guide](http://www.ledil.com/installation_guide)

## OPTICAL RESULTS (MEASURED):

### CITIZEN



LED CLUC11  
 FWHM / FWTM Asymmetric  
 Efficiency 86 %  
 Peak intensity 0.4 cd/lm  
 LEDs/each optic 1  
 Light colour/type White  
 Required components:



Light distribution files

### CREE LEDs


LED XP-G3  
 FWHM / FWTM Asymmetric  
 Efficiency 85 %  
 Peak intensity 0.4 cd/lm  
 LEDs/each optic 1  
 Light colour/type White  
 Required components:



Light distribution files

### inventronics

LED PL-LIN-Z5 1100 280x20  
 FWHM / FWTM Asymmetric  
 Efficiency 84 %  
 Peak intensity 0.4 cd/lm  
 LEDs/each optic 1  
 Light colour/type White  
 Required components:




Light distribution files

## OPTICAL RESULTS (MEASURED):

**inventronics**


LED PL-LIN-Z5 2000 280x20  
FWHM / FWTM Asymmetric  
Efficiency 81 %  
Peak intensity 0.4 cd/lm  
LEDs/each optic 1  
Light colour/type White  
Required components:



Light distribution files

**NICHIA**


LED NF2W757G-MT (Tunable White)  
FWHM / FWTM Asymmetric  
Efficiency 89 %  
Peak intensity 0.4 cd/lm  
LEDs/each optic 1  
Light colour/type Tunable White  
Required components:



Light distribution files

**NICHIA**

LED NFSW757H  
FWHM / FWTM Asymmetric  
Efficiency 89 %  
Peak intensity 0.4 cd/lm  
LEDs/each optic 1  
Light colour/type White  
Required components:




Light distribution files

## OPTICAL RESULTS (MEASURED):

### OSRAM

Opto Semiconductors

LED Duris E 2835  
FWHM / FWTM Asymmetric  
Efficiency 81 %  
Peak intensity 0.4 cd/lm  
LEDs/each optic 1  
Light colour/type White  
Required components:




Light distribution files

### OSRAM

Opto Semiconductors


LED Duris E 2835  
FWHM / FWTM Asymmetric  
Efficiency 84 %  
Peak intensity 0.4 cd/lm  
LEDs/each optic 1  
Light colour/type White  
Required components:



Light distribution files

### PHILIPS

LED Fortimo LED Strip 1ft 1100lm FC HV4 & LV4  
FWHM / FWTM Asymmetric  
Efficiency 84 %  
Peak intensity 0.4 cd/lm  
LEDs/each optic 1  
Light colour/type White  
Required components:




Light distribution files

## OPTICAL RESULTS (MEASURED):

### PHILIPS


**LED** Fortimo LED Strip 1ft 1100lm FC HV5 & LV5  
**FWHM / FWTM** Asymmetric  
**Efficiency** 88 %  
**Peak intensity** 0.5 cd/lm  
**LEDs/each optic** 1  
**Light colour/type** White  
**Required components:**



Light distribution files

### PHILIPS


**LED** Fortimo LED Strip 1ft 650lm FC HV4 & LV4  
**FWHM / FWTM** Asymmetric  
**Efficiency** 85 %  
**Peak intensity** 0.5 cd/lm  
**LEDs/each optic** 1  
**Light colour/type** White  
**Required components:**



Light distribution files

### PHILIPS

**LED** Fortimo LED Strip 1ft 650lm FC HV5 & LV5  
**FWHM / FWTM** Asymmetric  
**Efficiency** 88 %  
**Peak intensity** 0.5 cd/lm  
**LEDs/each optic** 1  
**Light colour/type** White  
**Required components:**




Light distribution files

## OPTICAL RESULTS (MEASURED):

### SAMSUNG


LED LM28xB Series  
 FWHM / FWTM Asymmetric  
 Efficiency 89 %  
 Peak intensity 0.5 cd/lm  
 LEDs/each optic 1  
 Light colour/type White  
 Required components:



Light distribution files

### SAMSUNG


LED LM301B  
 FWHM / FWTM Asymmetric  
 Efficiency 87 %  
 Peak intensity 0.4 cd/lm  
 LEDs/each optic 1  
 Light colour/type White  
 Required components:



Light distribution files

### SAMSUNG

LED LM561C  
 FWHM / FWTM Asymmetric  
 Efficiency 89 %  
 Peak intensity 0.5 cd/lm  
 LEDs/each optic 1  
 Light colour/type White  
 Required components:




Light distribution files

## OPTICAL RESULTS (MEASURED):

### SAMSUNG


LED LT-S282H  
FWHM / FWTM Asymmetric  
Efficiency 89 %  
Peak intensity 0.5 cd/lm  
LEDs/each optic 1  
Light colour/type White  
Required components:



Light distribution files

### SEOUL SEMICONDUCTOR


LED SEOUL DC 3528  
FWHM / FWTM Asymmetric  
Efficiency 89 %  
Peak intensity 0.4 cd/lm  
LEDs/each optic 1  
Light colour/type White  
Required components:



Light distribution files

### TRIDONIC

LED LLE 24x280mm 1250lm HV ADV5  
FWHM / FWTM Asymmetric  
Efficiency 84 %  
Peak intensity 0.4 cd/lm  
LEDs/each optic 1  
Light colour/type White  
Required components:




Light distribution files

## OPTICAL RESULTS (MEASURED):

### TRIDONIC


LED LLE 24x280mm 650lm HV ADV5  
FWHM / FWTM Asymmetric  
Efficiency 85 %  
Peak intensity 0.4 cd/lm  
LEDs/each optic 1  
Light colour/type White  
Required components:



Light distribution files

### TRIDONIC

LED LLE FLEX CC 14mm 1250lm ADV1  
FWHM / FWTM Asymmetric  
Efficiency 87 %  
Peak intensity 0.4 cd/lm  
LEDs/each optic 1  
Light colour/type White  
Required components:




Light distribution files

## OPTICAL RESULTS (SIMULATED):




LED LUXEON 2835 Architectural  
 FWHM / FWTM Asymmetric  
 Efficiency 86 %  
 Peak intensity 0.5 cd/lm  
 LEDs/each optic 1  
 Light colour/type White  
 Required components:



Light distribution files




LED LUXEON CSP HL1  
 FWHM / FWTM Asymmetric  
 Efficiency 88 %  
 Peak intensity 0.6 cd/lm  
 LEDs/each optic 1  
 Light colour/type White  
 Required components:



Light distribution files



LED NFSWE11A  
 FWHM / FWTM Asymmetric  
 Efficiency 83 %  
 Peak intensity 0.6 cd/lm  
 LEDs/each optic 1  
 Light colour/type White  
 Required components:




Light distribution files

## OPTICAL RESULTS (SIMULATED):

### SAMSUNG


LED LM301B  
 FWHM / FWTM Asymmetric  
 Efficiency 86 %  
 Peak intensity 0.5 cd/lm  
 LEDs/each optic 1  
 Light colour/type White  
 Required components:



Light distribution files

### SEOUL SEMICONDUCTOR


LED SEOUL DC 3030  
 FWHM / FWTM Asymmetric  
 Efficiency 84 %  
 Peak intensity 0.5 cd/lm  
 LEDs/each optic 1  
 Light colour/type White  
 Required components:



Light distribution files

### SEOUL SEMICONDUCTOR

LED Z5M4  
 FWHM / FWTM Asymmetric  
 Efficiency 84 %  
 Peak intensity 0.5 cd/lm  
 LEDs/each optic 1  
 Light colour/type White  
 Required components:



Light distribution files

## GENERAL INFORMATION:

NOTE: The typical beam angle will be changed by different color, chip size and chip position tolerance. The typical total beam angle is the full angle measured where the luminous intensity is half of the peak value.

Due to use of high power COB's with this product, special attention to proper thermal design is highly recommended. LEDiL has no liability for direct, indirect or consecutive damages arising from the LEDiL products being used outside of the recommended temperature range.

## MATERIALS:

As part of our continuous research and improvement processes, and to ensure the best possible quality and availability of our products, LEDiL reserves the right to change material grades without notice.

## PRODUCT DATA USER AGREEMENT AND DISCLAIMER:

The measured data in the provided downloadable LEDiL Product Datasheets and Mechanical 2D-Drawings is rounded and provided as reference for planning. LEDiL Oy's optical specifications have been verified by conducting performance testing of the products in accordance with the company's quality system. The reported data are averaged results of multiple measurements with typical variation. LEDiL Oy reserves the right to without prior notification make changes and improvements to its products.

LEDiL Oy assumes neither warranty, nor guarantee nor any other liability of any kind for the contents and correctness of the provided data. The provided data has been generated with highest diligence but the provided data may in reality not represent the complete possible variation range of all intrinsic parameters. Therefore, in certain cases a deviation from the provided data could occur.

LEDiL Oy reserves the right to undertake technical changes of its products without further notification which could lead to changes in the provided data. LEDiL Oy assumes no liability of any kind for the possible deviation from any provided data or any other damage resulting from the usage of the provided data.

The user agrees to this disclaimer and user agreement with the download or usage of the provided files.

LEDiL Oy  
Joensuunkatu 7  
FI-24100 SALO  
Finland

LEDiL Inc.  
228 West Page Street  
Suite D  
Sycamore IL 60178  
USA

Ledil Optics Technology  
(Shenzhen) Co., Ltd.  
# 405 , Block B  
Casic Motor Building  
Shenzhen 518057  
P.R.CHINA

Local sales and technical  
support  
[www.ledil.com/](http://www.ledil.com/)  
where\_to\_buy

Shipping locations  
Poznan, Poland  
Hong Kong, China

Distribution Partners  
[www.ledil.com/](http://www.ledil.com/)  
where\_to\_buy